



Actual

Project: JOB #3061

Turnkey Electric

Catalog Number: L-7-50-0-M
Product ID: 7TAG054330R0007
UPC Number: 72849491710
EAN Number: 05414363128540
Status: A

Standard Cable Tie, Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Black Color Nylon 6.6, Length of 188.85mm (7.44 Inches) for Bundle Diameter up to 44.45mm (1.75 Inches), Width of 4.73mm (0.186 Inch), Tensile Strength Rating of 222 Newtons (50 Pounds), Operating Temperature of -40 Degrees Celsius (-40 F) to 105 Degrees Celsius (221 F), Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, 1000 Pack

- Application Tools: ERG50, QC-100, L-200, L-400-C

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Brand Name	Catamount
Type	Standard
Standard	UL E49405
Width	0.186 in ; 4.73 mm
Length	7.435 in ; 188.85 mm
Thickness	0.053 in ; 1.35 mm
Bundle Diameter	0.0625 to 1.75 in ; 1.59 to 44.45 mm
Material	Nylon/Polyamide 6.6 Weather Resistant
Color	Black
Lock Mechanism	Plastic Pawl
Tensile Strength	50 pounds ; 220 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	4.73mm
Length belt/tape/tie	188.85mm
Tie thickness	1.35mm
Min. holding force	222N
Model	Internal toothing
Band closure	Plastic lip/-cam
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y

Packaging

Inner Quantity	1000
----------------	------

Inner Dimensions (inches)	17x12x3
Outer Quantity	10000
Outer Dimensions (inches)	18x12.9x13.4
Weight Uom	5 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000222
--------------------------------	------------

For further technical assistance, please contact us...

ABB Installation Products - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com