



102973-5 Product Details

[Share](#) | [Print](#) | [Email](#)


102973-5

TE Internal Number: 102973-5

Active

[View 3D PDF](#)

.100 inch AMPMODU Headers

5 of 6 EU RoHS/ELV Compliant (Find RoHS Compliant Alternates/Statement of Compliance)

Product Highlights:

- Connector
- Header Type = Breakaway
- 10 Positions
- Mating Post Length = 8.08 mm
- 2.54 mm Centerline

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [HEADER ASSY, MOD II, BREAKAWAY, DOUBLE ROW, .100X.10...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- [2D Drawing \(DXF, Version F\)](#)
- [3D Model \(IGES, Version F\)](#)
- [3D Model \(STEP, Version F\)](#)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector
- Mount Angle = Vertical
- PCB Mount Retention = Without
- Surface Mount Compatible = No
- Board Standoff = Without
- Mating Connector Lock = Without
- Post Size (mm [in]) = 0.64 [.025]

Mechanical Attachment:

- Mounting Ears = Without
- Panel Mount Retention = Without

Electrical Characteristics:

- Current Rating (A) = 3
- Insulation Resistance (MΩ) = 5,000
- Dielectric Withstanding Voltage (V) = 750

Termination Features:

- Termination Post Length (mm [in]) = 3.18 [0.125]
- Solder Tail Contact Plating = Tin-Lead over Nickel

Dimensions:

- Mating Post Length (mm [in]) = 8.08 [0.318]

Body Features:

- Header Type = Breakaway
- Number of Positions = 10
- Row-to-Row Spacing (mm [in]) = 2.54 [0.100]
- Number of Rows = 2
- Selectively Loaded = No
- Mount Type = Printed Circuit Board

Contact Features:

- Contact Plating, Mating Area, Material = Gold (15)
- Contact Shape = Square
- Contact Base Material = Phosphor Bronze

Housing Features:

- Centerline (mm [in]) = 2.54 [0.100]
- Housing Material = Thermoplastic - GF
- UL Flammability Rating = UL 94V-0

Industry Standards:

- RoHS/ELV Compliance = ELV compliant, 5 of 6 Compliant
- Lead Free Solder Processes = Wave solder capable to 240°C
- Approved Standards = UL E28476, CSA LR7189

Environmental:

- Operating Temperature (°C) = -65 - +105

Conditions for Usage:

- High Temperature Housing = No

Operation/Application:

- High Speed Serial Data Connector = No

Other:

- Brand = AMP
- Comment = Headers may be broken to desired number of positions using Hand Tool No. 91406-1, or Tool Kit No. 314818-1. Other tail lengths are available, consult Tyco Electronics.

