

Product Details for 1052985 - 1

SMA/QMA RF Connectors

[RoHS Compliant](#) (Statement of Compliance)

Product Highlights:

- ? Connector
- ? Jack
- ? Connector Type = SMA
- ? Terminate To Printed Circuit Board
- ? Body Style = Right Angle

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

No Image Available

1052985 - 1

 [Active](#)

Documentation & Additional Information

Product Drawings:

- ? [OSM HIGH FREQUENCY 2 HOLE FLANGE MOUNT RIGHT ANGLE J...](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Connector
- ? [Gender](#) = Jack
- ? [Connector Type](#) = SMA
- ? [Body Style](#) = Right Angle
- ? [Number of Panel Mount Holes](#) = 2
- ? [PCB Mount Angle](#) = Right Angle
- ? [Body Material](#) = Stainless Steel
- ? [Body Finish](#) = Gold over Nickel
- ? [Center Contact](#) = With
- ? [Retractable Collar](#) = Without
- ? [Safety Wire Holes](#) = Without
- ? Dielectric Material = TFE Fluorocarbon
- ? Comment = High frequency.

Mechanical Attachment:

- ? [Panel Attachment](#) = With
- ? [Panel Attachment Method](#) = Flange
- ? [Panel Attachment Style](#) = Front Mount
- ? Impedance (?) = 50

Electrical Characteristics:

- ? Frequency = DC to 18 GHz
- ? Insulation Resistance (M?) = 10,000

Body Related Features:

- ? [Length \(mm \[in\]\)](#) = 29.00 [1.142]

Contact Related Features:

- ? Contact Type = Straight
- ? Center Contact Material = Beryllium Copper
- ? Center Contact Plating = Gold over Copper

Industry Standards:

- ? Government/Industry Qualification = No
- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C, Reflow solder capable to 245°C, Reflow solder capable to 260°C, Pin -in -Paste capable to 245°C, Pin in -Paste capable to 260°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? [Terminate To](#) = Printed Circuit Board

Other:

- ? Brand = AMP