


Product Details for 1 -5380758 -0



1 -5380758 -0

[Active](#)

Discrete Sockets

[RoHS Compliant \(Statement of Compliance\)](#)

Product Highlights:

- ? Socket
- ? Mating Pin Dia. Range = .91 - 1.30 mm
- ? Socket Length = 6.65 mm
- ? Sleeve Style = Closed Bottom
- ? Tin Sleeve Plating

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [REUSABLE COMPONENT RECEPTACLE](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files: ([CAD Format & Compression Information](#))

- ? [3D Model](#) (STEP, Version A)
- ? [3D Model](#) (IGES, Version A)
- ? [2D Drawing](#) (DXF, Version A)

[List all Documents](#)

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? Product Type = Socket
- ? [Socket Length \(mm \[in\]\)](#) = 6.65 [0.262]
- ? [Sleeve Style](#) = Closed Bottom
- ? [Sealant](#) = Without
- ? Sleeve Material = Copper
- ? Recommended Hole Size (mm [in]) = 2.26 [0.089]

Body Related Features:

- ? [Mating Pin Dia. Range \(mm \[in\]\)](#) = 0.91 - 1.30 [0.036 - 0.051]

Contact Related Features:

- ? [Sleeve Plating](#) = Tin
- ? [Contact Spring Plating](#) = Tin
- ? [Contact Material](#) = Beryllium Copper

Configuration Related Features:

- ? [Insertion Method](#) = Hand/Semi -Automatic

Industry Standards:

- ? Government/Industry Qualification = No
- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C, Reflow solder capable to 245°C, Reflow solder capable to 260°C, Pin -in -Paste capable to 245°C, Pin in -Paste capable to 260°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Operation/Application:

- ? Application = Testing/Reusable

Packaging Related Features:

- ? [Packaging Method](#) = Loose Piece

Other:

- ? Brand = AMP