


1757819-6 Product Details

[Share](#) | [Print](#) | [Email](#)


1757819-6

Subminiature D Pins/Sockets for MIL-C-24308 and MIL-C-39029

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector
- Product Series = 109
- Connector Style = Plug
- Contact Type = Pin
- Density = Standard

[View all Features](#)

TE Internal Number: 1757819-6
 Active

[View 3D PDF](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none"> • AMPLIMITE PLUG ASSY,SIZE 1 THRU 5 SERIES 109 WITH ZI... (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files: (CAD Format & Compression Information)</p> <ul style="list-style-type: none"> • 2D Drawing (DXF, Version F) • 3D Model (IGES, Version F) • 3D Model (STEP, Version F) 	<p>Additional Information:</p> <ul style="list-style-type: none"> • Product Line Information <p>Additional Product Images:</p> <ul style="list-style-type: none"> • Insert Arrangement <p>Related Products:</p> <ul style="list-style-type: none"> • Tooling

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> • Product Type = Connector • Product Series = 109 • Shell Size = 1 • Shell Material = Steel • Termination Method to Wire/Cable = Crimp • Mounting Hole Diameter (mm [in]) = 3.05 [.120] <p>Body Features:</p> <ul style="list-style-type: none"> • Number of Positions = 9 • Blindmate = No • Non-Magnetic = No • Rear Grommet = No • Power/Signal/Coax Combination = No • Shell Plating = Zinc • Mount Style = Mounting Holes • Retention Clip Material = Stainless Steel <p>Contact Features:</p> <ul style="list-style-type: none"> • Contact Type = Pin • Contact Size = 20 • Contact Style = Crimp Snap-in 	<p>Housing Features:</p> <ul style="list-style-type: none"> • Connector Style = Plug <p>Configuration Features:</p> <ul style="list-style-type: none"> • Density = Standard <p>Industry Standards:</p> <ul style="list-style-type: none"> • Government/Industry Qualification = Yes • Government/Industry Part Number = M24308/4-1 • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Wave solder capable to 260°C, Wave solder capable to 240°C, Wave solder capable to 265°C • RoHS/ELV Compliance History = Always was RoHS compliant • NASA Qualification = No <p>Conditions for Usage:</p> <ul style="list-style-type: none"> • Applies To = Wire/Cable <p>Other:</p> <ul style="list-style-type: none"> • Brand = AMP • Comment = Size 20 contacts supplied with connectors are loose piece.

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference Products](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

