


1053137-1 Product Details


[Live Product Chat](#)


1053137-1
(2058-3100-00)

TE Internal Number: 1053137-1

 [Active](#)

SMA/QMA RF Connectors

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Connector
- Jack
- Connector Type = SMA
- Terminate To Printed Circuit Board
- Without Snap-Lock

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)

Documentation & Additional Information

Product Drawings:

- [OSM BULKHEAD JACK HERMETICALLY SEALED .020 DIA. PIN](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector
- [Gender](#) = Jack
- [Connector Type](#) = SMA
- [Body Style](#) = Straight
- [PCB Mount Angle](#) = Vertical
- [Body Material](#) = Stainless Steel
- [Body Finish](#) = Gold
- [Center Contact](#) = With
- Dielectric Material = PTFE Fluorocarbon
- Comment = Hermetically Sealed

Mechanical Attachment:

- [Panel Attachment](#) = With
- [Panel Attachment Method](#) = Bulkhead
- [Panel Attachment Style](#) = Front Mount

Electrical Characteristics:

- Impedance (Ω) = 50
- Frequency = DC - 18 GHz
- Insulation Resistance ($M\Omega$) = 5,000

Body Related Features:

- Snap-Lock = Without
- [Length \(mm \[in\]\)](#) = 17.20 [0.677]
- O-Ring Material = Silicone Rubber

Contact Related Features:

- Center Contact Material = Beryllium Copper
- Center Contact Plating = Gold

Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C, Reflow solder capable to 245°C, Reflow solder capable to 260°C, Pin-in-Paste capable to 245°C, Pin-in-Paste capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- [Terminate To](#) = Printed Circuit Board

Other:

- Brand = AMP

 [Provide Website Feedback](#) | [Need Help?](#)