


5 - 208550 - 1 Product Details



5 - 208550 - 1

Active

Subminiature D Pin/Socket Connectors for MIL - C- 24308 and MIL - C- 39029

Always EU RoHS/ELV Compliant ( Statement of Compliance )

Product Highlights:

- ? Connector
- ? Product Series = 109
- ? Density = Standard
- ? Terminate To Coaxial Cable, Terminate To Printed Circuit Board, Terminate To Wire
- ? Insert Arrangement = 36C4

View all Features | Find Similar Products

Live Product Chat US Only 8:30am - 5pm ET, Mon - Fri

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Documentation & Additional Information	
<p><b>Product Drawings:</b></p> <p>? None Available</p> <p><b>Catalog Pages/Data Sheets:</b></p> <p>? None Available</p> <p><b>Product Specifications:</b></p> <p>? None Available</p> <p><b>Application Specifications:</b></p> <p>? None Available</p> <p><b>Instruction Sheets:</b></p> <p>? None Available</p> <p><b>CAD Files:</b></p> <p>? None Available</p>	<p><b>Additional Information:</b></p> <p>? <a href="#">Product Line Information</a></p> <p><b>Additional Product Images:</b></p> <p>? <a href="#">PCB Layout</a></p> <p><b>Related Products:</b></p> <p>? <a href="#">Tooling</a></p>

Product Features (Please use the Product Drawing for all design activity)	
<p><b>Product Type Features:</b></p> <p>? <a href="#">Product Type</a> = Connector</p> <p>? <a href="#">Product Series</a> = 109</p> <p>? <a href="#">Gender</a> = Receptacle</p> <p>? <a href="#">Shell Size</a> = 5</p> <p>? <a href="#">Shell Material</a> = Steel</p> <p>? Mounting Hole Diameter (mm [in]) = 3.05 [.120]</p> <p>? Comment = Cable clamp/strain relief hardware cannot be used with these arrangements.</p> <p><b>Body Related Features:</b></p> <p>? <a href="#">Insert Arrangement</a> = 36C4</p> <p>? <a href="#">Blindmate</a> = No</p> <p>? <a href="#">Non -Magnetic</a> = No</p> <p>? <a href="#">Sockets</a> = Without</p> <p>? <a href="#">Rear Grommet</a> = No</p> <p>? <a href="#">Power/Signal/Coax Combination</a> = Yes</p> <p>? <a href="#">Shell Plating</a> = Zinc</p> <p>? Mount Style = Mounting Holes</p> <p>? Retention Clip Material = Stainless Steel</p>	<p><b>Contact Related Features:</b></p> <p>? <a href="#">Contact Size</a> = 20</p> <p><b>Configuration Related Features:</b></p> <p>? <a href="#">Density</a> = Standard</p> <p><b>Industry Standards:</b></p> <p>? Government/Industry Qualification = No</p> <p>? <a href="#">RoHS/ELV Compliance</a> = RoHS compliant, ELV compliant</p> <p>? <a href="#">Lead Free Solder Processes</a> = Wave solder capable to 240°C, Wave solder capable to 260° C, Wave solder capable to 265°C</p> <p>? RoHS/ELV Compliance History = Always was RoHS compliant</p> <p>? NASA Qualification = No</p> <p><b>Conditions for Usage:</b></p> <p>? Terminate To = Coaxial Cable, Printed Circuit Board, Wire</p> <p><b>Other:</b></p> <p>? Brand = AMP</p>