


Product Details for 5225059 - 3



5225059 - 3

[Active](#)

SHV RF Connectors

[RoHS Compliant \(Statement of Compliance\)](#)

Product Highlights:

- ? Connector
- ? Jack
- ? Coaxial Cable Type (RG/U or Mfg.) = 59, 59A, 59B, 62, 62A, 62B, 124, 140, 210, Belden 9209, Belden 9268, Belden 9291
- ? Coaxial Cable Termination Type = Crimp
- ? Nickel Body Plating

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [JACK, BULKHEAD, SHV](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Connector
- ? [Gender](#) = Jack
- ? Panel Thickness (mm [in]) = 6.35 [0.250]
- ? Dielectric Material = TEFLON
- ? Comment = Connector Cable Range Selection Code -G.

Mechanical Attachment:

- ? [Panel Attachment](#) = With
- ? [Panel Attachment Method](#) = Bulkhead

Termination Related Features:

- ? Coaxial Cable Termination Type = Crimp

Body Related Features:

- ? [Body Plating](#) = Nickel

Contact Related Features:

- ? Center Contact Plating = Gold

Configuration Related Features:

- ? [Coaxial Cable Type \(RG/U or Mfg.\)](#) = 59, 59A, 59B, 62, 62A, 62B, 124, 140, 210, Belden 9209, Belden 9268, Belden 9291

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? Terminate To = Coaxial Cable

Other:

- ? Brand = AMP