


532436-1 Product Details

[Share](#) | [Print](#) | [Email](#)


532436-1

TE Internal Number: 532436-1
Active

[View 3D PDF](#)

AMP-HDI (Four Beam) & TBC (Twin Beam) Connectors

5 of 6 EU RoHS/ELV Compliant ([Find RoHS Compliant Alternates/Statement of Compliance](#))

Product Highlights:

- Connector
- Plug
- 100 Positions
- PCB Mount Style = Through Hole
- PCB Mounting Orientation = Vertical

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [View Connectors \(3\)](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [HDI, 4 ROW, PIN ASSEMBLY, 4.83 \[.190\] LONG SOLDER PL...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [Connector, Interconnect, High Density](#) (PDF, English)

Application Specifications:

- [AMP-HDI Connectors](#) (PDF, English)

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version S)
- [3D Model](#) (IGES, Version S)
- [3D Model](#) (STEP, Version S)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)
- [Connectors \(3\)](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector
- [Gender](#) = Plug
- [PCB Mount Style](#) = Through Hole
- [PCB Mounting Orientation](#) = Vertical
- [Make First / Break Last](#) = No
- [PCB Mount Retention](#) = Without

Termination Features:

- [Termination Post Length \(mm \[in\]\)](#) = 4.83 [0.190]
- [Solder Tail Contact Plating](#) = Tin

Body Features:

- [Number of Positions](#) = 100
- [Number of Rows](#) = 4
- [Centerline \(mm \[in\]\)](#) = 2.54 [0.100]

Contact Features:

- [Contact Configuration](#) = Four-Beam
- [Contact Plating, Mating Area, Material](#) = Gold (30)
- Contact Base Material = Phosphor Bronze
- Underplate Material = Nickel

Housing Features:

- [Mating Alignment](#) = Without
- [Housing Material](#) = PPS
- [Housing Color](#) = Brown
- [Housing Material Temperature](#) = High

Configuration Features:

- [Center Guide](#) = Without

Industry Standards:

- [Government/Industry Qualification](#) = No
- [RoHS/ELV Compliance](#) = ELV compliant, 5 of 6 Compliant
- [Lead Free Solder Processes](#) = Not suitable for lead free processing

Other:

- Brand = AMP

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference Products](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

