


Product Details for 225687 - 2



225687 - 2

[Active](#)

Twin Threaded RF Connectors

[RoHS Compliant \(Statement of Compliance\)](#)

Product Highlights:

- ? Connector
- ? Plug
- ? Coaxial Cable Type (RG/U or Mfg.) = 108, 108A (Ctr. Cond. 7/0126), Belden 8759
- ? Terminate To Coaxial Cable
- ? Without Panel Attachment

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [receptacle threaded twin series](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? [AMP* THEADED - TYPE TWIN COAXICON* CONNECTORS](#) (PDF, English)

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? Product Type = Connector
- ? [Gender](#) = Plug
- ? Crimp Type = Single
- ? Dielectric Material = Polypropylene

Mechanical Attachment:

- ? Panel Attachment = Without

Termination Related Features:

- ? Coaxial Cable Termination Type = Crimp

Body Related Features:

- ? [Body Plating](#) = Nickel

Contact Related Features:

- ? Center Contact Plating = Gold

Configuration Related Features:

- ? [Coaxial Cable Type \(RG/U or Mfg.\)](#) = 108, 108A (Ctr. Cond. 7/0126), Belden 8759

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? [Terminate To](#) = Coaxial Cable

Other:

- ? Brand = AMP