

Product Details for 487925 - 8



487925 - 8

[Active](#)

Flexible Film Connectors

[RoHS Compliant \(Statement of Compliance\)](#)

Product Highlights:

- ? Connector
- ? 2.54 mm Centerline
- ? Connector Type = ZIF -Line
- ? Number of Positions = 11
- ? Number of Rows = Single

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [CONNECTOR ASSEMBLY, .100CL, ZIF -LINE 50](#) (TIF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files: ([CAD Format & Compression Information](#))

- ? [3D Model](#) (STEP, Version F)
- ? [3D Model](#) (IGES, Version F)
- ? [2D Drawing](#) (DXF, Version F)

[List all Documents](#)

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

Product Features

(Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Connector
- ? [Connector Type](#) = ZIF -Line
- ? [Number of Positions](#) = 11
- ? [PCB Thickness \(mm \[in\]\)](#) = 2.36 [0.093]
- ? [Mating Connector Lock](#) = Without
- ? [Mating Polarization](#) = Without
- ? [Mounting Ears](#) = Without
- ? Flame Retardant = Yes
- ? Color = Black

Mechanical Attachment:

- ? [Panel Attachment](#) = Without

Body Related Features:

- ? [Centerline \(mm \[in\]\)](#) = 2.54 [0.100]
- ? [Number of Rows](#) = Single
- ? [Cable Entry Angle](#) = Vertical

Contact Related Features:

- ? Contact Mating Area Plating = Tin
- ? Contact Material = Phosphor Bronze

Housing Related Features:

- ? Housing Material = Thermoplastic
- ? Housing Flammability Rating = UL 94V -0

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Converted to comply with RoHS directive

Conditions for Usage:

- ? [Terminate To](#) = Printed Circuit Board

Other:

- ? Brand = AMP