


Catalog

- ▶ [Home](#)
- ▶ [Part Number Search](#)
- ▶ [Document Search](#)
- ▶ [CAD Model Search](#)
- ▶ [Text Search](#)
- ▶ [Alternate/Lead Free Part Search](#)
- ▶ [Multiple Part Comparison](#)
- ▶ [Alphabetical Search](#)
- ▶ [Brand Search](#)
- ▶ [Industry Product Search](#)
- ▶ [Product Type Search](#)
- ▶ [Product Family Search](#)
- ▶ [Competitor Cross Reference](#)
- ▶ [Lead Free Solutions](#)
- ▶ [Tool Search](#)
- ▶ [Help/Glossary](#)

AMPMODU

 **.100 & .150 Centerline Through Hole Headers**

5-826632-0  [Active](#)

**Directive 2002/95/EC
Compliant**
[RoHS Compliant](#)
**(Tyco Electronics P/N:
5-826632-0)**
[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> ▶ General Info ▶ Sales Info ▶ Assembly Subcontractors 	<ul style="list-style-type: none"> ▶ Pricing ▶ Product Availability 	<ul style="list-style-type: none"> ▶ Tooling

Searchable Features:

Brand:	AMP
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Process:	Not reviewed for lead free solder process
Header Type:	Breakaway
No. of Rows:	Dual
No. of Positions:	100
Profile:	Standard
Centerline, Matrix (mm [in]):	2.54 [.100]
Mount Angle:	Vertical
Selectively Loaded:	No
PCB Retention Feature:	Without
Surface Mount Compatible:	No

Other Properties:

RoHS/ELV Compliance History:	Always was compliant
Contact Material:	Brass
Housing Material:	Thermoplastic Polyester
Contact Termination Area Plating:	Tin
Housing Flammability Rating:	UL 94V-0
Packaging Method:	Box
Packaging Quantity:	150

Contact Mating Area Plating:	Gold (30)
Board Standoff:	Without
Mounting Ears:	Without
Panel Attachment:	No
Mating Connector Lock:	Without
High Temperature Housing:	No
High Speed Serial Data Connector:	No
Termination Post Length (mm [in]):	3.20 [0.126]
Mount Type:	PC Board

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International, Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)