


Product Details for 6339169 - 3



No Image Available

6339169 - 3

[Active](#)

PCB Mounted Jacks - Single Port, Multi - port and Stacked

[RoHS Compliant \(Statement of Compliance\)](#)

Product Highlights:

- ? Jack
- ? Multiple Port Configuration
- ? 1 x 8 Jack Configuration
- ? Jack Type = RJ45
- ? Number of Positions = 8

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [ASSEMBLY, MULTI - PORT, 1X8, 8 POSITION, SHIELDED, WAVE P...](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? [High Performance Modular Plugs & Jacks, PCB Mounted](#) (PDF, English)

Application Specifications:

- ? [Modular Jacks](#) (PDF, English)

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Jack
- ? [Jack Type](#) = RJ45
- ? [Number of Positions](#) = 8
- ? [PCB Mount Angle](#) = Side Entry (Right Angle)
- ? [PCB Mount Style](#) = Thru Hole
- ? [PCB Termination Type](#) = Solder
- ? [Shielded](#) = Yes
- ? [Performance Category](#) = Cat 5
- ? Number of Contacts Loaded = 8
- ? [Grounding Options](#) = Panel Ground and PCB Ground
- ? [Panel Stops](#) = Without
- ? [Keyed](#) = No
- ? [Profile](#) = Standard
- ? IR Reflow Compatible = Yes
- ? [Color](#) = Black
- ? Shield Material = Copper Zinc Alloy
- ? Comment = Recommended applications: Fast Ethernet, 10Base - T Ethernet, and 10/100 Base T Ethernet (Cat 5 on two pair 1/2, 3/6).

Mechanical Attachment:

- ? [Jack Configuration](#) = 1 x 8
- ? [Panel Attachment](#) = Without

Termination Related Features:

- ? [Solder Tail Plating](#) = Tin over Nickel

Body Related Features:

- ? Port Configuration = Multiple
- ? [Inverted Jack Face](#) = No
- ? [LED](#) = Without
- ? Shield Plating = Nickel
- ? Number of PCB Ground Tabs = 3
- ? [PCB Tail Length \(mm \[in\]\)](#) = 3.05 [0.120]
- ? Number of Contacts Loaded, RJ45 (8 Positions) = 8
- ? PCB Ground Tab Location (mm [in]) = 4.57 [0.180]

Contact Related Features:

- ? [Contact Mating Area Plating](#) = Gold (50) over Nickel (50)
- ? Contact Material = Phosphor Bronze

Housing Related Features:

- ? Number of Panel Ground Tabs = 27
- ? Housing Material = Polyester (PCT)
- ? Housing Flammability Rating = UL 94V - 0

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Operation/Application:

- ? Shield Information = Wave panel grounds.

Packaging Related Features:

- ? Packaging Method = Tray
- ? Packaging Quantity = 10

Other:

- ? Brand = AMP