


## 8 - 1393644 - 3 Product Details



**8 - 1393644 - 3**

[Active](#)

### Eurocard Type C

[Converted to EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

#### Product Highlights:

- ? Type C Connectors
- ? Plug
- ? Number of Positions = 96
- ? Rows Loaded = A, B, C
- ? Terminate To Printed Circuit Board

[View all Features](#) | [Find Similar Products](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [pin assembly eurocard](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? None Available

#### Application Specifications:

- ? None Available

#### Instruction Sheets:

- ? None Available

#### CAD Files:

- ? None Available

#### Additional Information:

- ? [Product Line Information](#)

#### Related Products:

- ? [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? [Product Type](#) = Type C Connectors
- ? [Gender](#) = Plug
- ? [Number of Positions](#) = 96
- ? [PCB Retention Feature](#) = Yes
- ? [PCB Mount Angle](#) = Right Angle
- ? [Post Type](#) = Solder Post
- ? [Size](#) = Standard
- ? [Make First / Break Last](#) = No
- ? [DIN Level](#) = II
- ? [Mounting Ears](#) = With
- ? Toolless (Flat Rock) = No
- ? Color = Gray

#### Termination Related Features:

- ? [Termination \(Solder\) Post Length \(mm \[in\]\)](#) = 3.00 [0.118]

#### Body Related Features:

- ? [Rows Loaded](#) = A, B, C
- ? [PCB Retention Method](#) = Boardlock(s)
- ? [Contact Cross Section \(mm \[in\]\)](#) = 0.60 [.024] Sq.

#### Contact Related Features:

- ? Contact Material = Copper Alloy

#### Housing Related Features:

- ? Housing Material = Polyester GF 30%
- ? Housing Flammability Rating = UL 94V -0

#### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? [Flux - Tight Coating](#) = Without
- ? RoHS/ELV Compliance History = Converted to comply with RoHS directive

#### Conditions for Usage:

- ? [Terminate To](#) = Printed Circuit Board
- ? [High Temperature Housing](#) = No

#### Other:

- ? Brand = AMP