

5145263-2 Product Details

[Share](#) | [Print](#) | [Email](#)



5145263-2

TE Internal Number: 5145263-2
✔ **Active**

[View 3D PDF](#)

AGP, NLX, Slot 1 Connectors (Standard Edge 1mm)

✔ [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Connector
- 124 Positions
- Bus Type = AGP (Accelerated Graphic Port)
- Connector Design = Solder Tail
- Termination Post Length = 2.70 mm

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [ASSEMBLY, 124 POSITION 1mm, CARD EDGE CONNECTOR \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing \(DXF, Version A\)](#)
- [3D Model \(IGES, Version A\)](#)
- [3D Model \(STEP, Version A\)](#)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector
- [Bus Type](#) = AGP (Accelerated Graphic Port)
- [Connector Design](#) = Solder Tail
- PCB Mounting Orientation = Vertical

Termination Features:

- [Termination Post Length \(mm \[in\]\)](#) = 2.70 [0.106]
- Solder Tail Contact Plating = Tin-Lead over Nickel

Body Features:

- [Number of Positions](#) = 124
- [Centerline \(mm \[in\]\)](#) = 1.00 [0.039]

Contact Features:

- [Contact Plating, Mating Area, Material](#) = Gold (15)
- Contact Base Material = Brass

Housing Features:

- Housing Material = Nylon 66/6
- Housing Color = Brown

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 260°C, Wave solder capable to 240°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = AMP

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference Products](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

[▶](#)

