


281838-4 Product Details

Have a Question?
Chat with a Product Information Specialist



281838-4

TE Internal Number: 281838-4

Active

View 3D PDF

.100 AMPMODU Headers, Housings & Contacts

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector
- Housing
- Connector Style = Receptacle
- Contact Type = Receptacle
- 2.54 mm Centerline

View all Features

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Documentation & Additional Information

Product Drawings:

- SINGLE ROW HOUSING FOR HE 13-14 COSI CONTACT (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- MODULAR HEADERS AND PLUGS ACCORDING TO IEC 60603-8 S... (PDF, French)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- 2D Drawing (DXF, Version B)
- 3D Model (IGES, Version B)
- 3D Model (STEP, Version B)

List all Documents

Additional Information:

- Product Line Information

Related Products:

- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector
- Connector Type = Housing
- Termination Method to Wire/Cable = Crimp, Insulation Displacement Crimp (IDC)
- Mating Connector Lock = Without
- Mating Polarization = Without
- Connector Series = HE13 / HE14
- Keyed = No

Body Related Features:

- Centerline (mm [in]) = 2.54 [0.100]
- Row-to-Row Spacing (mm [in]) = 2.54 [0.100]
- Number of Positions = 4
- Number of Rows = 1

Contact Related Features:

- Contact Type = Receptacle

Housing Related Features:

- Connector Style = Receptacle
- Housing Color = Blue
- UL Flammability Rating = UL 94V-0
- Housing Material = PBT - GF

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- Packaging Method = Loose Piece

Other:

- Brand = AMP

BOOKMARK

Corporate Information

- Who We Are
- Investors
- News Room
- Supplier Portal
- Careers

Quick Links

- Check Distributor Inventory
- Cross Reference
- Find Documents & Drawings
- Product Compliance Support Center
- Site Map

Customer Support

- Email or Chat with Us
- Find a Phone Number
- Search Knowledge Base
- Manage Your Account

Sign up for our eNewsletter

Enter your email address

Follow Us On:



Visit Us On:

