




- Product Facts ■ 7600 Series Programmable Shunts use conventional .100 x .300 [2.54x7.62] DIP leg spacing
- Post Shunts are used to common pairs of .025 [0.64] square posts, .025 [0.64] diameter round posts and .022 x .026 [0.56 x 0.66] formed posts

Shunts



Tyco Electronics offers a variety of high quality shunts for low cost manual programming. AMP 7600 Series Programmable Shunts are designed on the standard .100 x .300 [2.54 x 7.62] DIP spacing.

AMP DIP Shunts are a highly reliable, low cost means of manually programming various types of electrical/electronic equipment. The shunt consists of a series of conductive straps packaged in a DIP configuration. The straps can be retained intact for a closed circuit or broken with a hand tool to produce an open circuit. AMP Post Shunts mate with any common pairs of square, rectangular and round posts. Post shunts come in two-position low profile, 2 mm miniature, tandem spring, dual beam, and multiposition versions.

Among the options available are choices of gold or tin plating, beryllium copper or phosphor bronze contact material and shunts with 94V-0 rated housing spaces on .079 [2.00], .100 [2.54] and .200 [5.08] centers with the low profile series requiring only .250 [6.35] clearance from the pc board. All AMP shunts feature onepiece construction for high reliability. All have high normal forces for excellent electrical continuity. For added reliability, Tandem Spring and Dual Beam Shunts have two points of contact in each receptacle.

Catalog 1307819 Revised 6-04

www.tycoelectronics.com

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-5-729-0425



Standard Shunt Standard Pressure

Material and Finish:

UL 94V-0 rated Contacts - Brass

Housing - Glass-filled polyester,

Finish - Selectively plated .000100

min. tin/lead on solder area over .000050 min. nickel on entire contact

Contact Lead Spacing -.100 x .300 [2.54x7.62]

Programming Hand Tool Part No. 435862-1

of programming DIP shunts. It is rugged, light-weight and dependable. No special skills are required to use this tool.


Machine Insertable Shunt (Compatible with commercially available IC insertion equipment)


mounting surface Housing Color — Black Programming Tool — See below

AMPMODU Interconnection System




Dual In-Line Package (DIP) Shunts — 7600 Series





Contact Lead Spacing -.100 x .300 [2.54x7.62]

Programming Tool — None required (5 to 10 lbs. [22.2 to 44.4N] required to manually program each shunt position)



No. of	Dimension A		Standard Shunt	Machine Insertable
Positions	inch	mm	Standard Pressure	Shunt
4	.400	10.16	435704-4	_
6	.600	15.24	435704-6	_
7	.700	17.78	435704-7	_
8	.800	20.32	435704-8	436860-7
9	.900	22.86	435704-9	_
10	1.000	25.40	1-435704-0	_
12	1.200	30.48	1-435704-2	_



326 Catalog 1307819

Revised 6-04

www.tycoelectronics.com

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents. to change.

Dimensions are shown for reference purposes only. Specifications subject

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-5-729-0425





Product Facts

- One-piece contact construction
- High normal forces
- 94V-0 rated housings
- Gold inlay, gold plate or tin plate over nickel
- Stackable
- Those post shunts indicated are recognized under the component program of Underwriters Laboratories Inc., 91 File No. E28476 and certified by the **Canadian Standards** Association (SP) File No. LR 7189

Tandem Spring Shunts

- Two points of contact provide extra reliability
- Shunts accept posts as short as .175 [4.45]; posts bottom at .330 [8.38]

2mm Mini Shunts

- Stackable on 2mm contact centerline
- Low profile
- Available in strips of 10

Material and Finish - Low Profile, Multiposition and 2mm Shunts

Housing - Glass-filled thermoplastic, UL 94V-0 rated Contacts - Beryllium copper or phosphor bronze Finish - .000050 [0.00127] nickel with gold plate in contact area or tin plate overall


Material and Finish - Tandem Spring Shunts

Housing – Nylon, UL 94V-0 rated Contacts - Phosphor Bronze Finish - .000030 [0.00076] nickel with gold inlay in the contact area or tin plate overall



2-Position, Low Profile Shunts


Economy Shunt .100 [2.54] Centerline



			Part Nu	mbers	
Configuration	Housing Color	Gold Plate ¹ .000015 [0.00038]	Gold Flash ¹ .000005 [0.00013]	Tin Plate .000100 [0.00254]	Gold Plate .000030 [0.00076]
Strip of 10	Blue	382811-2	_	_	_
Strip of 10	Black	382811-6	382811-8	382811-5	2-382811-0
Strip of 10	Red	382811-9	_	_	_
Loose Piece	Black	1-382811-6	1-382811-8	_	_

In contact area

Standard Housing Shunt .200[5.08] Centerline



		Part Numbers	
Housing Color	Gold Plate ¹ .000015 [0.00038]	Gold Plate ¹ .000030 [0.00076]	Tin Plate .000100 [0.00254]
Black	531230-2	531230-3	531230-1
	Color	Color .000015 [0.00038]	Housing Color Gold Plate ¹ Gold Plate ¹ 000015 .000030 [0.00038] [0.00076]

Shunts

327

Catalog 1307819 Revised 6-04

www.tycoelectronics.com

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-5-729-0425





Electronics

Post Shunts (Continued)


2-Position, Low Profile Shunts (Novo) (Continued)

Handle Shunt .100 [2.54] Centerline


2 mm Mini-Shunt .079 [2.00] Centerline

(SP®


119.



		Loose Piece Pa	art Numbers		_
Housing Color	Gold Plate ¹ .000015 [0.00038]	Gold Plate ¹ .000030 [0.00076]	Gold Plate ¹ .000050 [0.00127]	Tin Plate .000100 [0.00254]	Туре
Black	881545-1	881545-2	881545-3	881545-4	Open Top
Black	880584-1	880584-2	880584-3	880584-4	Closed Top
¹ In contact area					



		Part Numbers		
Configuration	Housing Color	Gold Plate ¹ .000015 [0.00038]	Gold Plate ¹ .000030 [0.00076]	
Strip of 10	Black	382575-2	382575-3	
¹ In contact area				



		Part N	umbers	
Configuration	Housing Color	Gold Plate ¹ .000015 [0.00038]	Gold Plate ¹ .000030 [0.00076]	Туре
Strip of 10	Black	390088-2	390088-1	Open Top
Strip of 10	Blue	390088-4	390088-3	Open Top
Strip of 10	Yellow	_	390088-5	Open Top
In contact area	reliow	—	390088-5	Open

Dual Beam Shunt

328

Catalog 1307819 Revised 6-04

www.tycoelectronics.com

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-5-729-0425






Electronics

Tandem Spring Shunt

.100 [2.54] Centerline








	Part Nu	mbers
Housing Color	Gold Inlay ¹ .000030 [0.00076]	TinPlate .000100 [0.00254]
Black	530153-2	2-530153-2
¹ In contact area		

Multiposition Shunts for.025 [0.64] Square Posts

.200 [5.08] Centerline



Housing – Glass-filled polyester Contacts – Beryllium Copper Finish – .000030 [.00076] gold in contact area over .000050 [.00127] nickel on entire contact Current Rating – 2.5 amps



	Dimension A		Housing	Part
Size	inch	mm	Color	Number
2x2	.246	6.25	Black	390102-1
2x2	.246	6.25	Red	390102-3
2x3	.396	10.01	Black	390102-2

329

Catalog 1307819 Revised 6-04

www.tycoelectronics.com

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-5-729-0425 South America: 55-11-3611-1514 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-141-810-8967

8





Performance Specifications

Dual In-Line Package (DIP) Shunts – 7600 Series

Current Rating:

Standard pressure– 2 amperes for +20°C rise above ambient (one conductor per shunt Machine insertable –1 ampere for +20°C rise above ambient (one conductor per shunt) **Insulation Resistance:** 1x 10¹⁰ ohms min. at 100 VDC **Dielectric Withstanding Voltage:** 500 VDC min.

Capacitance: 2 picofarads max. between adjacent straps

Temperature Rating: -55°C to +105°C

Terminal Strength (Bend Test): Two 45° bend cycles per MIL-STD-202, Method 211, Condition B Solder Bridaina:

Cut straps can be reconnected by solder bridging. Solder bridging recommendations are:

- •Use low temperature solder (60/40 tin/lead)
- •Use solder tip approximately 1/32 [0.79] in diameter
- Do not let solder tip come in contact with plastic material

Post Shunts

Current Rating: 3 amperes max. unless otherwise noted Temperature Rating: -65°C to +105°C (gold) -40°C to +85°C (tin)

Technical Documents

Various technical documents are available for your use:

Product Specifications describe technical performance characteristics and verification tests. They are intended for the Design, Component and Quality Engineer.

Dual In-Line Package (DIP) Shunts
2mm Mini Shunt
Economy Shunt, Multiposition Shunt
Dual Beam Shunt
Low Profile Shunt
Tandem Spring Shunt
Novo Shunt with Handle

Application Specifications describe requirements for using the product in its intended application and/or crimping information. They are intended for the Packaging and Design Engineer and the Machine Setup Person.

114-1045	Tandem Spring Shunt
114-1054	Dual In-Line Package (DIP) Shunts
114-1059	Economy Shunt, Dual Beam Shunt, Low Profile Shunt, Multiposition
	Shunt
114-1074	2mm Mini Shunt

Instruction Sheets provide instructions for assembling or applying the product. They are intended for the Manufacturing Assembler or Operator.

408-7768	Dual In-Line Package (DIP) Shunts
408-3208	Tandem Spring Shunt
408-3230	Economy Shunt, Dual Beam Shunt, Low Profile Shunt
408-3251	Multiposition Shunt
408-3276	2mm Mini Shunt
408-3276	2mm Mini Shunt

330

Catalog 1307819 Revised 6-04

www.tycoelectronics.com specified. '

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-5-729-0425