


1761633-2 Product Details

Have a Question?

Chat with a Product Information Specialist



1761633-2

TE Internal Number: 1761633-2

Active

Pin and Pinless Headers (AMP-LATCH)

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Preloaded
- Housing Gender = Header - Pin
- Header Type = Pin Header
- AMP-LATCH Product Line
- Low Profile

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)
[Request Sample](#)
[Find Similar Products](#)
[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [HEADER ASSEMBLY, VERTICAL, 40 POS, LOW PROFILE, SELE...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Line = AMP-LATCH
- Profile = Low
- PCB Mount Angle = Vertical
- PCB Mount Retention = Without
- Mating Polarization Type = Center, Dual Polarizing Bar
- Mating Connector Lock = Without
- Housing Style = 4-Sided
- Ejection Latches = Without
- Post Size (mm [in]) = 0.64 [.025]
- Shrouded = Yes
- Comment = Post # Omitted - Row T 11, Row S None

Termination Related Features:

- Termination Post Length (mm [in]) = 3.05 [0.120]
- Solder Tail Contact Plating = Tin

Body Related Features:

- Header Type = Pin Header
- Number of Positions = 40
- Centerline, Matrix (mm [in]) = 2.54 x 2.54 [.100 x .100]
- Daisy Chain = With

Contact Related Features:

- Preloaded = Yes
- Contact Plating, Mating Area, Material = Gold (15)
- Contact Shape = Square

Housing Related Features:

- Housing Gender = Header - Pin
- Housing Material = Nylon
- UL Flammability Rating = UL 94V-0
- Housing Color = Black

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Temperature Rating = Standard

Other:

- Brand = AMP

BOOKMARK

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address



Follow us on:

