

V23092A1905A301 Product Details

[Share](#) [Print](#) [Email](#)


V23092A1905A301

(5-1393236-7)

TE Internal Number: 5-1393236-7

 [Active](#)

Industrial Relays (General Purpose)

 [Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Relay Type = Power
- Relay Style = PCB
- SNR Series
- Contact Arrangement = 1 Form C, SPDT, 1 C/O
- Contact - Rated Current = 6 A

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Series](#) = SNR
- [Termination Type](#) = Through Hole

Electrical Characteristics:

- [Contact - Rated Current \(A\)](#) = 6
- [Coil Resistance \(Ω\)](#) = 119
- [Coil - Rated Power \(mW\)](#) = 170
- [Actuating System](#) = DC
- [Input Voltage \(VDC\)](#) = 5
- Insulation - Special Features = None

Body Features:

- Polarized = No

Contact Features:

- Relay Type = Power
- [Mounting Options](#) = PC Board
- [Enclosure Type](#) = Enclosed
- [Contact Base Material](#) = Silver Tin Oxide
- Approx. Dimensions (L x W x H) (mm [in]) = 5.00 x 28.00 x 15.00 [.197 x 1.103 x .591]
- Terminal Assignment = 1 Form C

Configuration Features:

- Relay Style = PCB
- [Contact Arrangement](#) = 1 Form C, SPDT, 1 C/O
- [Coil - Magnetic System](#) = Monostable
- [Coil Suppression Diode](#) = Without
- [Coil Selection Criteria](#) = Nominal Voltage
- Coil Latching = Without
- Status Indicator = None

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C
- RoHS/ELV Compliance History = Converted to comply with RoHS directive
- Approved Standards = UL Recognized, CSA Certified, VDE Component Mark

Other:

- Brand = Schrack

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

