


1 - 390263 - 1 Product Details



1 - 390263 - 1

 [Active](#)

DIP Sockets

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? DIP Socket
- ? Number of Positions = 28
- ? Row-to -Row Spacing = 15.24 mm
- ? Thru Hole
- ? Mount Style = Vertical

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [DIP SOCKET, 15.24 CENTERLINE OTC STYLE](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features

(Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = DIP Socket
- ? [Number of Positions](#) = 28
- ? [Profile](#) = Over -The -Component
- ? [Frame Style](#) = Open
- ? [Leg Style](#) = Straight
- ? Color = Black

Electrical Characteristics:

- ? Insulation Resistance (M?) = 10,000
- ? Contact Resistance (m?) = 30

Termination Related Features:

- ? [Termination \(Solder\) Post Length \(mm \[in\]\)](#) = 3.00 [0.118]

Body Related Features:

- ? [Row-to -Row Spacing \(mm \[in\]\)](#) = 15.24 [0.600]
- ? [Mount Style](#) = Vertical
- ? [Centerline \(mm \[in\]\)](#) = 2.54 [0.100]

Contact Related Features:

- ? [Contact Mount](#) = Thru Hole
- ? [Contact Material](#) = Phosphor Bronze
- ? [Contact Mating Area Plating](#) = Tin
- ? [Contact Style](#) = Stamped + Formed
- ? [Mating Contact Type](#) = Dual Leaf

Housing Related Features:

- ? Housing Material = Thermoplastic

Configuration Related Features:

- ? [Height Above PC Board \(mm \[in\]\)](#) = 5.10 [0.200]

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? Temperature Range (°C) = -40 – + 105

Packaging Related Features:

- ? [Packaging Method](#) = Tube

Other:

- ? Brand = AMP