





🗓 Share

Quick Links

Pricing & Availability

Product Feature Selector

Contact Us About This Product

Search for Tooling



🚞 Print

🔤 Email

Industries Products About TE My Account Innovation Support Center Resources

Home > Products > Modular Jacks & Plugs > Product Feature Selector > Product Details

## 1116504-2 Product Details



#### Product Highlights:

- Connector
- Preloaded
- Single Port Configuration
- 1 x 1 Jack Configuration
- Jack Type = RJ45

View all Features



🔁 View 3D PDF

1116504-2











Additional Information:

Related Products:

Tooling

Product Line Information

#### Documentation & Additional Information

#### Product Drawings:

MODULAR JACK ASSEMBLY, 8 POSITION, 10mm (PDF, English)

#### Catalog Pages/Data Sheets:

None Available

#### Product Specifications:

High Performance Modular Plugs & Jacks, PCB Mounted (PDF, English)

#### Application Specifications:

Modular Jacks (PDF, English)

#### Instruction Sheets:

None Available

#### CAD Files: (CAD Format & Compression Information)

- 2D Drawing (DXF, Version J)
- 3D Model (IGES, Version J)
- 3D Model (STEP, Version J)

List all Documents

# Product Features (Please use the Product Drawing for all design activity)

## Product Type Features:

- Product Type = Connector
- Jack Type = RJ45.
- PCB Mounting Orientation = Side Entry (Right Angle)
- PCB Mount Style = Through Hole
- Termination Method to PC Board = Solder
- Performance Category = Cat 5
- LED = Without
- Grounding Options = Without
- Panel Stops = Without
- Keyed = No.
- Profile = Low
- Color = Black
- Latch Style = Standard

## Mechanical Attachment:

- Panel Mount Retention = With
- Flanged = No.

## **Electrical Characteristics:**

Shielded = No.

## Termination Features:

Solder Tail Contact Plating = Tin over Nickel

## Dimensions:

- Height (mm [in]) = 9.30 [0.366]
- PCB Tail Length (mm [in]) = 3.48 [0.137]
- PCB Thickness, Recommended (mm [in]) = 1.57 [0.062]

## Body Features:

Inverted Jack Face = No

## Contact Features:

- Contact Plating, Mating Area, Material = Gold (50)
- Contact Base Material = Phosphor Bronze

## **Housing Features:**

- Housing Material = High Temperature Nylon
- UL Flammability Rating = UL 94V-0

## Configuration Features:

- Preloaded = Yes
- Port Configuration = Single
- Jack Configuration = 1 x 1
- Number of Positions = 8
- Number of Contacts Loaded = 8.

## **Industry Standards:**

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

## Packaging Features:

Packaging Method = Tray

## Product Availability:

Region = Asia, North America

## Other:

- Brand = AMP
- Comment = Recommended applications: Fast Ethernet, 10Base-T Ethernet, and 10/100 Base-T Ethernet (Cat 5 on two pair 1/2, 3/6).

## Corporate Information

About TE Investors News Room Supplier Portal Careers

Quick Links

Distributor Inventory Product Cross Reference Documents & Drawings

Product Compliance Support Center

Site Map

Customer Support Email or Chat With Us Find a Phone Number Knowledge Base

Manage Your Account

Keep Me Informed









Terms & Conditions Privacy Policy