

1 - 1337448 - 0 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



1 - 1337448 - 0

[Active](#)

BNC RF Connectors

[Converted to EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Connector
- ? Connector Type = BNC
- ? Jack
- ? Body Style = Bulkhead
- ? Not Surface Mountable

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [BNC BULKHEAD SOCKET FRONT MOUNT + TAG 50 OHM](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Connector
- ? [Connector Type](#) = BNC
- ? [Gender](#) = Jack
- ? Body Style = Bulkhead
- ? [Grade](#) = Professional
- ? [Body Material](#) = Brass
- ? [Sealed](#) = No
- ? [Isolated](#) = No
- ? [Dielectric Material](#) = PTFE
- ? Number of Ports = 1
- ? Panel Thickness (mm [in]) = 1.50 – 2.90 [0.059 – 0.114]
- ? Flats Dimension = 11.0 A/F
- ? Solder Terminal = With
- ? Comment = With Solder Tag

Mechanical Attachment:

- ? Surface Mountable = No
- ? [Panel Attachment](#) = With
- ? Panel Attachment Method = Hex Nut
- ? Panel Attachment Style = Front Mount
- ? Panel Cutout = 8.9mm x 9.7mm D -Shape
- ? Flange Dimension [Dia.] (mm [in]) = 12.5 [0.492]
- ? Flange and Thread Material = Brass
- ? Lockwasher Material = Brass
- ? Lockwasher Plating = Nickel

Electrical Characteristics:

- ? [Connector Impedance \(?\)](#) = 50
- ? Frequency = DC - 4 GHz

Body Related Features:

- ? [Hardware Included](#) = No
- ? [Body Plating](#) = Nickel
- ? [Polarized](#) = No

Contact Related Features:

- ? [Center Contact Material](#) = Brass
- ? [Center Contact Plating](#) = Gold

Industry Standards:

- ? Government/Industry Qualification = No
- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Converted to comply with RoHS directive

Conditions for Usage:

- ? Military Style Number = UG - 1094/U
- ? Operating Temperature (Max.) (°C) = 165

Packaging Related Features:

- ? Packaging Method = Individual
- ? Packaging Quantity = 50

Other:

- ? Brand = Greenpar