


DETAIL M
(FOR 7-1437045-6 ONLY)

onlinecomponents.com



RECOMMENDED PC BOARD LAYOUT
(VIEWED FROM CONNECTOR SIDE)

- △ HOUSING: PBT, UL94V-0, COLOR BLUE.
- △ POSTS: PHOSPHOR BRONZE.
- △ POSTS: 0.00076[.000030] MIN GOLD ON MATING AREA, 0.00254[.000100] MIN TIN-LEAD ON SOLDER END, ALL OVER 0.00127[.000050] MIN NICKEL ON ENTIRE POST.
- △ DATUMS S & T TO BE ESTABLISHED BY CUSTOMER.
- △ NO KEYING SLOT ON THIS END FOR 6, 8, 10, 12 & 14 POSITION ASSEMBLIES.
- △ NO KEYING SLOT ON THIS END FOR 6, 8 & 10 POSITION ASSEMBLIES.

	E	D	C	B	A	NO OF POS	PART NUMBER
OBSOLETE	2.59 [.102]	78.74 [3.100]	31	86.36 [3.400]	88.90 [3.500]	64	4-1437046-3
OBSOLETE	2.59 [.102]	73.66 [2.900]	29	81.28 [3.200]	83.82 [3.300]	60	3-1437046-1
OBSOLETE	4.19 [.165]	60.96 [2.400]	24	68.58 [2.700]	71.12 [2.800]	50	1-1437046-4
	2.59 [.102]	60.96 [2.400]	24	68.58 [2.700]	71.12 [2.800]	50	1437046-6
	2.59 [.102]	53.34 [2.100]	21	60.96 [2.400]	63.50 [2.500]	44	9-1437045-9
	4.19 [.165]	48.26 [1.900]	19	55.88 [2.200]	58.42 [2.300]	40	8-1437045-1
SEE DETAIL M	2.59 [.102]	48.26 [1.900]	19	55.88 [2.200]	58.42 [2.300]	40	7-1437045-6
	2.59 [.102]	48.26 [1.900]	19	55.88 [2.200]	58.42 [2.300]	40	7-1437045-3
	2.59 [.102]	43.18 [1.700]	17	50.80 [2.000]	53.34 [2.100]	36	6-1437045-5
	4.19 [.165]	40.64 [1.600]	16	48.26 [1.900]	50.80 [2.000]	34	5-1437045-3
	2.59 [.102]	40.64 [1.600]	16	48.26 [1.900]	50.80 [2.000]	34	4-1437045-7
	2.59 [.102]	35.56 [1.400]	14	43.18 [1.700]	45.72 [1.800]	30	2-1437050-3
OBSOLETE	4.19 [.165]	30.48 [1.200]	12	38.10 [1.500]	40.64 [1.600]	26	3-1437045-1
	2.59 [.102]	30.48 [1.200]	12	38.10 [1.500]	40.64 [1.600]	26	2-1437045-5
	4.19 [.165]	27.94 [1.100]	11	35.56 [1.400]	38.10 [1.500]	24	1-1437045-8
	2.59 [.102]	27.94 [1.100]	11	35.56 [1.400]	38.10 [1.500]	24	1-1437045-6
	4.19 [.165]	22.86 [.900]	9	30.48 [1.200]	33.02 [1.300]	20	1437045-1
	2.59 [.102]	22.86 [.900]	9	30.48 [1.200]	33.02 [1.300]	20	9-1437044-5
	4.19 [.165]	17.78 [.700]	7	25.40 [1.000]	27.94 [1.100]	16	7-1437044-9
	2.59 [.102]	17.78 [.700]	7	25.40 [1.000]	27.94 [1.100]	16	7-1437044-3
	4.19 [.165]	15.24 [.600]	6	22.86 [.900]	25.40 [1.000]	14	5-1437044-8
	2.59 [.102]	15.24 [.600]	6	22.86 [.900]	25.40 [1.000]	14	5-1437044-3
	2.59 [.102]	12.70 [.500]	5	20.32 [.800]	22.86 [.900]	12	2-1437049-2
OBSOLETE	4.19 [.165]	10.16 [.400]	4	17.78 [.700]	20.32 [.800]	10	4-1437044-2
	2.59 [.102]	10.16 [.400]	4	17.78 [.700]	20.32 [.800]	10	3-1437044-7
OBSOLETE	2.59 [.102]	7.62 [.300]	3	15.24 [.600]	17.78 [.700]	8	2-1437054-9
	4.19 [.165]	5.08 [.200]	2	12.70 [.500]	15.24 [.600]	6	2-1437044-6
	2.59 [.102]	5.08 [.200]	2	12.70 [.500]	15.24 [.600]	6	2-1437044-4

**COPYRIGHT 2005
 TYCO ELECTRONICS CORP
 ALL RIGHTS RESERVED**

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM[INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DIN 1 GERACE 11JAN05	tyco Tyco Electronics Corporation Harrisburg, Pa 17105
0 PLC ± -	1 PLC ± -	2 PLC ± -	3 PLC ± -
4 PLC ± 0.13[.005]	ANGLES ± -	APVD M.WALMSLEY 11JAN05	NAME M.WALMSLEY
MATERIAL	FINISH	APPLICATION SPEC	PRODUCT SPEC
		SIZE	CAGE CODE
		WEIGHT	DRAWING NO
		CUSTOMER DRAWING	SCALE 4:1
			RESTRICTED TO
			SHEET 1 OF 1
			REV C

APPLICATION SPEC: A1 00779 ©=2-1437044-4