

- <u>Product Type</u> = Receptacle

Contact Related Features:

<u>Contact Mating Area Plating Material</u> = Gold

• <u>Connector Series</u> = Mod II	(30)
 Number of Positions = 34 	 Contact Material = Phosphor Bronze
• <u>Profile</u> = Standard	 Contact Type = Short Point
• Mount Angle = Vertical	
 <u>Mounting Pattern (mm [in])</u> = 2.54 x 3.81 [.100 x .150] <u>Sealed</u> = No <u>Holddown Feature</u> = Without 	 Housing Related Features: Housing Entry Style = Top Housing Material = Thermoplastic Housing Flammability Rating = UL 94V-0
 PCB Retention Feature = No 	 Housing Color = Black
 Closed Entry = With 	
• Board Standoff = With	 Industry Standards: Government/Industry Qualification = No
Mechanical Attachment: • <u>Stackable</u> = No	 <u>RoHS/ELV Compliance</u> = Not ELV/RoHS compliant <u>Lead Free Solder Processes</u> = Wave solder
Termination Related Features:	capable to 240°C
 Termination Method = Through Hole <u>Termination (Solder) Post Length (mm [in])</u> = 3.05 [0.120] Solder Tail Contact Plating = Tin-Lead over Nickel 	Conditions for Usage: • High Temperature Compatible = No Other: • Brand = AMP
Body Related Features:	
 <u>Number of Rows</u> = Dual 	
 <u>Connector Height (mm [in])</u> = 5.03 [0.198] <u>Centerline, Matrix (mm [in])</u> = 2.54 x 2.54 [.100 x .100] 	
	I

Provide Website Feedback | Need Help?

Home | Customer Support | Suppliers | Site Map | Privacy Policy | Browser Support © 2008 Tyco Electronics Corporation All Rights Reserved