

## 1734451 -2 Product Details

**Live Product Chat** US Only  
8:30am - 5pm ET, Mon - Fri



**1734451 -2**

✓ [Active](#)

### Removable Memory Products

[Always EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

#### Product Highlights:

- ? Number of Positions = 50
- ? Format = CompactFlash™
- ? CompactFlash™ Product Type = Header Only
- ? Header Type = Type I, Type II
- ? Lead Type = Surface Mount - Inline leads

[View all Features](#) | [Find Similar Products](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [PIN HEADER SLIM TYPE, 50 POS, TOP BOARD, COMPACT FLA...](#) (PDF, Japanese)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? [COMPACT FLASH CARD, 1.27mm\(.050"\) PITCH](#) (PDF, English)

#### Application Specifications:

- ? None Available

#### Instruction Sheets:

- ? None Available

#### CAD Files: ( [CAD Format & Compression Information](#) )

- ? [2D Drawing](#) (DXF, Version B)
- ? [3D Model](#) (IGES, Version B)
- ? [3D Model](#) (STEP, Version B)

[List all Documents](#)

#### Related Products:

- ? [Tooling](#)

### Product Features

(Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? [Number of Positions](#) = 50
- ? Mount Angle = Right Angle
- ? Holddowns = With
- ? Shielded = No
- ? Color = White

#### Mechanical Attachment:

- ? Mounting Style = Top (Printed Circuit Board)

#### Termination Related Features:

- ? Solder Tail Contact Plating = Tin

#### Body Related Features:

- ? CompactFlash™ Product Type = Header Only
- ? Header Type = Type I, Type II
- ? Lead Type = Surface Mount - Inline leads
- ? Number of Rows = Dual
- ? Centerline (mm [in]) = 1.27 [0.050]

#### Contact Related Features:

- ? Contact Mating Area Plating Material = Gold (30)
- ? Vacuum Tape = Without
- ? Region = Americas
- ? Contact Material = Brass
- ? Contact Underplating = Nickel

#### Housing Related Features:

- ? Housing Material = Thermoplastic
- ? Housing Flammability Rating = UL 94V -0

#### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- ? Format = CompactFlash™

#### Packaging Related Features:

- ? Packaging Method = Tray

#### Other:

- ? Brand = AMP