

Catalog

- [Home](#)
- [Part Number Search](#)
- [Document Search](#)
- [CAD Model Search](#)
- [Text Search](#)
- [Alternate/Lead Free Part Search](#)
- [Multiple Part Comparison](#)
- [Alphabetical Search](#)
- [Brand Search](#)
- [Industry Product Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Competitor Cross Reference](#)
- [Lead Free Solutions](#)
- [Tool Search](#)
- [Help/Glossary](#)

Flexible Film Products

↳ FLEXSTRIP® Jumpers

tyco FSN-21A-10  [Active](#)
Electronics

**Directive 2002/95/EC
Compliant**

[RoHS Compliant](#)

(Tyco Electronics P/N: 6-1437139-7)

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> ↳ General Info ↳ Sales Info 	<ul style="list-style-type: none"> ↳ Pricing ↳ Product Availability 	<ul style="list-style-type: none"> ↳ Tooling

Searchable Features:

Brand:	Tyco Electronics
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Process:	Wave solder capable to 240°C, Wave solder capable to 265°C
Insulation Material:	Nomex
Centerline (mm [in]):	2.54 [0.100]
Insulation Length (mm [in]):	25.40 [1.000]
Pin Arrangement (left):	A
Pin Arrangement (right):	A
No. of Conductors:	10

Other Properties:

RoHS/ELV Compliance History:	Always was RoHS compliant
Operating Temperature (°C [°F]):	-40 – +125 [-40 – +257]
Current Rating (Amps.):	3
Impedance (Ω):	107
Voltage Rating (VAC):	300

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International, Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)