

## 1775855-1 Product Details

Live Product Chat



**1775855-1**

TE Part Number: 1775855-1

Active

Add to Part List

### Universal Serial Bus (USB) Connectors

Always EU RoHS/ELV Compliant (Statement of Compliance)

#### Product Highlights:

- Size = Standard
- A-RJ45 Series
- Receptacle
- Without Locking Feature
- 1 Ports

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

### Documentation & Additional Information

#### Product Drawings:

- [Modular Jack RJ45 stacked over USB Conn. Dip Type \(TIF, English\)](#)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing \(DXF, Version A\)](#)
- [3D Model \(IGES, Version A\)](#)
- [3D Model \(STEP, Version A\)](#)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Size = Standard
- Gender = Receptacle
- Number of Ports = 1
- Orientation = Right Angle
- PCB Thickness (mm [in]) = 1.60 [0.063]
- Number of Positions = 4
- Comment = RJ-45 over USB

#### Mechanical Attachment:

- Mount Location = Top

#### Termination Related Features:

- Termination Method = Solder to PC Board
- Tail Length (mm [in]) = 2.8 [0.11]

#### Body Related Features:

- Series = A-RJ45
- Locking Feature = Without
- [Panel Ground](#) = Without
- PCB Retention Method = Kinked Legs, Straight Legs
- Shell Plating = Matte Tin over Nickel
- Pick and Place Cover = None
- Locating Posts = Without

#### Contact Related Features:

- Contact Termination Type = Through Hole
- [Contact Mating Area Plating Material](#) = Gold
- Contact Mating Area Plating Thickness = Flash

#### Housing Related Features:

- [Housing Color](#) = Black

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- Terminate To = Printed Circuit Board

#### Packaging Related Features:

- [Packaging Method](#) = Tray

#### Other:

- Brand = Tyco Electronics