


208062-1 Product Details

[Share](#) | [Print](#) | [Email](#)


208062-1

TE Internal Number: 208062-1
✔ Active

[View 3D PDF](#)

5mm (.197") Centerline, 600 V, 14 A max. (Metrimate)

Not EU RoHS or ELV Compliant (Find RoHS Compliant Alternates)

Product Highlights:

- Accessory
- Accessory Type = Commoning Device Assembly
- Square Grid Connector Configuration
- 36 Positions
- Without Coaxial Socket

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)
[Request Sample](#)
[Find Similar Products](#)
[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [COMMONING DEVICE ASSEMBLY, 36 POSITION, METRIMATE \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- [2D Drawing \(DXF, Version H\)](#)
- [3D Model \(IGES, Version H\)](#)
- [3D Model \(STEP, Version H\)](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Accessory
- Accessory Type = Commoning Device Assembly
- Keyed = No
- 8/32 Insert = No
- PCB Mount Retention = Without

Mechanical Attachment:

- [Mounting Ears](#) = Without
- [Jackscrew](#) = Without

Body Features:

- Coaxial Socket = Without
- Pin Header Housing Color = Red
- Pin Header Housing Material = Thermoplastic

Contact Features:

- Contact Plating, Mating Area, Material = Tin-Lead
- Contact Base Material = Copper Alloy

Housing Features:

- Housing Material = Thermoplastic - GF
- Housing Color = Black

Configuration Features:

- [Connector Configuration](#) = Square Grid
- [Number of Positions](#) = 36

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C

Other:

- Brand = AMP
- Comment = Positions 1-8 commoned, 9-16 commoned, 17-24 commoned, 25-32 commoned, and 33-36 commoned together; Mates with plug 207019-1

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference Products](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address [▶](#)

