


## 182734-2 Product Details

[Share](#) [Print](#) [Email](#)


182734-2

TE Internal Number: 182734-2

 **Active**

 [View 3D PDF](#)

### .100 AMPMODU Headers, Housings & Contacts

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Contact
- Contact Type = Socket
- Crimp Termination Method to Wire/Cable, Insulation Displacement Crimp (IDC) Termination Method to Wire/Cable
- Applies To Wire/Cable
- Wire Insulation Diameter = .80 - 1.50 mm

[View all Features](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [HE14 SYSTEM RECEPTACLE](#) (PDF, English)
- [HE1402 CONNECTOR \(TIN VERSION\)](#) (PDF, English)
- [HE 1302 CONNECTOR \(GOLD VERSION\) CRIMP CONTACT \(AWG ...\)](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- [CONTACT RECEPTACLE CRIMP HE13 HE14](#) (PDF, English)

#### Instruction Sheets:

- None Available

#### CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version G)
- [3D Model](#) (IGES, Version G)
- [3D Model](#) (STEP, Version G)

[List all Documents](#)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Type = Contact
- [Termination Method to Wire/Cable](#) = Crimp, Insulation Displacement Crimp (IDC)
- Wire Insulation Diameter (mm [in]) = 0.80 - 1.50 [0.032 - 0.059]
- [Connector Series](#) = HE13 / HE14

#### Body Features:

- [Wire Range \(mm \[AWG\]\)](#) = 0.08-0.24<sup>2</sup> [28-24]

#### Contact Features:

- Contact Type = Socket
- [Contact Plating, Mating Area, Material](#) = Tin
- Contact Base Material = Phosphor Bronze

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- [Applies To](#) = Wire/Cable

#### Packaging Features:

- Packaging Method = Loose Piece

#### Other:

- Brand = AMP

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

