




What can we help you find?

Home > Products > Removable Memory Products > Product Feature Selector > Product Details

5788643-1 Product Details

Share Print Email



5788643-1

TE Internal Number: 5788643-1
 Active

View 3D PDF

Removable Memory Products

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- 50 Positions
- Format = CompactFlash™
- CompactFlash™ Product Type = Header Only
- Header Type = Type I, Type II
- Lead Type = Surface Mount - Staggered leads

[View all Features](#)

Quick Links

- ▶ Pricing & Availability
- ▶ Search for Tooling
- ▶ Product Feature Selector
- ▶ Contact Us About This Product

Add to My Part List Request Sample Find Similar Products Buy Product

Documentation & Additional Information

Product Drawings:

- PIN HEADER ASSEMBLY, VERTICAL, 50 POSITION, SURFACE ... (PDF, English)
- ASSY, 1.00MM FFC CONN SMT, V (NON-ZIF) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- Interconnection System, AMP Memory Card, Recpt/Hdr A... (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- 2D Drawing (DXF, Version 0)
- 3D Model (IGES, Version 0)
- 3D Model (STEP, Version 0)

[List all Documents](#)

Related Products:

- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Mount Angle = Vertical
- Color = Black

Mechanical Attachment:

- Mounting Style = Top (Printed Circuit Board)
- Holddowns = Without

Electrical Characteristics:

- Shielded = No

Termination Features:

- Solder Tail Contact Plating = Tin

Body Features:

- CompactFlash™ Product Type = Header Only
- Header Type = Type I, Type II
- Lead Type = Surface Mount - Staggered leads
- PCB Offset (mm [in]) = 0.00 [0.000]

Contact Features:

- Contact Plating, Mating Area, Material = Gold (30)
- Vacuum Tape = Without
- Contact Base Material = Brass
- Underplate Material = Nickel

Housing Features:

- Housing Material = Liquid Crystal Polymer (LCP)
- UL Flammability Rating = UL 94V-0
- Centerline (mm [in]) = 1.27 [0.050]

Configuration Features:

- Number of Positions = 50
- Number of Rows = Dual

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Format = CompactFlash™

Packaging Features:

- Packaging Method = Tube

Other:

- Brand = AMP

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

