

2-221128 -9 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



2-221128 -9

BNC RF Connectors

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- ? Connector
- ? Connector Type = BNC
- ? Plug
- ? Terminate To Coaxial Cable
- ? Coaxial Cable Termination Type = Crimp

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

STOP [Obsolete](#)
[Search for Replacement Parts](#)

Documentation & Additional Information

Product Drawings:

- ? [PLUG, COMMERCIAL BNC](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? [COAXICON 50 -Ohm BNC RF Series Commercial Plug \(Hex C...](#) (PDF, English)

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features

(Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Connector
- ? [Connector Type](#) = BNC
- ? [Gender](#) = Plug
- ? [Crimp Type](#) = Hex
- ? [Body Style](#) = Straight
- ? [Grade](#) = Commercial
- ? [Body Insulation](#) = Without
- ? [Sealed](#) = No
- ? [Isolated](#) = No
- ? [Dielectric Material](#) = Polyethylene
- ? [Coupling Nut Material](#) = Brass
- ? Number of Ports = 1
- ? Solder Terminal = Without

Mechanical Attachment:

- ? Surface Mountable = No
- ? Panel Attachment = Without

Electrical Characteristics:

- ? [Connector Impedance \(?\)](#) = 50

Termination Related Features:

- ? [Coaxial Cable Termination Type](#) = Crimp

Body Related Features:

- ? [Hardware Included](#) = No
- ? [Body Plating](#) = Nickel
- ? [Polarized](#) = No

Contact Related Features:

- ? [Center Contact Material](#) = Brass
- ? [Center Contact Plating](#) = Gold

Configuration Related Features:

- ? [Coaxial Cable Type \(RG/U or Mfg.\)](#) = 188, 316, JIS 1.5D -2V, JIS 1.5D -XV, JIS 1.5D -XVS

Industry Standards:

- ? Government/Industry Qualification = No
- ? [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process

Conditions for Usage:

- ? [Terminate To](#) = Coaxial Cable

Packaging Related Features:

- ? Contact Packaging Method = Single

Other:

- ? Brand = AMP