


2-292253 -2 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



2-292253 -2

[Active](#)

2mm AMP CT

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Connector
- ? Connector Type = MT (Mass Termination)
- ? Mating Type = Header
- ? Number of Positions = 2
- ? Number of Rows = 1

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [POST HEADER ASS'Y HORIZONTAL TYPE \(AMP CT CONNECTOR....](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files: ([CAD Format & Compression Information](#))

- ? [2D Drawing](#) (DXF, Version 0)
- ? [3D Model](#) (IGES, Version 0)
- ? [3D Model](#) (STEP, Version 0)

[List all Documents](#)

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Connector
- ? [Connector Type](#) = MT (Mass Termination)
- ? [Mating Type](#) = Header
- ? [Number of Positions](#) = 2
- ? [PCB Mount Style](#) = Thru Hole
- ? [PCB Mount Angle](#) = Right Angle
- ? [PCB Polarization](#) = No
- ? [PCB Retention Feature](#) = Yes

Mechanical Attachment:

- ? [Panel Attachment](#) = Without

Termination Related Features:

- ? Solder Tail Contact Plating = Tin

Body Related Features:

- ? [Number of Rows](#) = 1
- ? [Header Body Style](#) = Standard
- ? [PCB Retention Method](#) = Retention Solder Tails
- ? Centerline (mm [in]) = 2.00 [0.079]

Contact Related Features:

- ? Contact Material = Brass
- ? Contact Mating Area Plating = Tin

Housing Related Features:

- ? [Housing Material](#) = Nylon
- ? [Housing Color](#) = Blue
- ? Housing Flammability Rating = UL 94V -0

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? [Terminate To](#) = Printed Circuit Board

Other:

- ? Brand = AMP