


## 146839 -3 Product Details

**Live Product Chat** US Only  
8:30am - 5pm ET, Mon - Fri



**146839 -3**

[Active](#)

### Removable Memory Products

[Always EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

#### Product Highlights:

- ? Number of Positions = 50
- ? Format = CompactFlash™
- ? CompactFlash™ Product Type = Header Only
- ? Header Type = Type I
- ? Lead Type = Surface Mount - Staggered leads

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [PIN HEADER ASSEMBLY, VERTICAL, 50 POSN, SURFACE MOUNT,](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? None Available

#### Application Specifications:

- ? None Available

#### Instruction Sheets:

- ? None Available

#### CAD Files: ( [CAD Format & Compression Information](#) )

- ? [2D Drawing](#) (DXF, Version D)
- ? [3D Model](#) (IGES, Version D)
- ? [3D Model](#) (STEP, Version D)

#### Related Products:

- ? [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? [Number of Positions](#) = 50
- ? Mount Angle = Vertical
- ? Holddowns = Without
- ? Shielded = No
- ? Color = Black

#### Termination Related Features:

- ? Solder Tail Contact Plating = Tin

#### Body Related Features:

- ? CompactFlash™ Product Type = Header Only
- ? Header Type = Type I
- ? Lead Type = Surface Mount - Staggered leads
- ? Number of Rows = Dual
- ? Centerline (mm [in]) = 1.27 [0.050]

#### Contact Related Features:

- ? Contact Mating Area Plating Material = Gold (30)
- ? Vacuum Tape = With
- ? Region = Americas
- ? Contact Material = Brass
- ? Contact Underplating = Nickel (50)

#### Housing Related Features:

- ? Housing Material = Liquid Crystal Polymer (LCP)
- ? Housing Flammability Rating = UL 94V -0

#### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- ? Format = CompactFlash™

#### Packaging Related Features:

- ? Packaging Method = Tube

#### Other:

- ? Brand = AMP