


1-534236-5 Product Details

[Live Product Chat](#)



1-534236-5

TE Part Number: 1-534236-5

Active

[Add to Part List](#)

.100 inch AMPMODU Receptacles

[5 of 6 EU RoHS/ELV Compliant](#) ([Find RoHS Compliant Alternates/Statement of Compliance](#))

Product Highlights:

- Receptacle
- Mod II
- Number of Positions = 30
- Number of Rows = Dual
- Standard Profile

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- [ASSEMBLY, MOD II DOUBLE ROW, .100 X .100 C/L, VERTIC...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- [AMPMODU Mod II and Mod IV Printed Circuit Board Conn...](#) (PDF, English)

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Receptacle
- [Connector Series](#) = Mod II
- [Number of Positions](#) = 30
- [Profile](#) = Standard
- [Mount Angle](#) = Vertical
- [Mounting Pattern \(mm \[in\]\)](#) = 2.54 x 3.81 [.100 x .150]
- [Sealed](#) = No
- [Holddown Feature](#) = Without
- PCB Retention Feature = No
- Closed Entry = With
- Board Standoff = With

Mechanical Attachment:

- [Stackable](#) = No

Termination Related Features:

- Termination Method = Through Hole
- [Termination \(Solder\) Post Length \(mm \[in\]\)](#) = 3.05 [0.120]
- Solder Tail Contact Plating = Tin-Lead over Nickel

Body Related Features:

- [Number of Rows](#) = Dual
- [Connector Height \(mm \[in\]\)](#) = 5.03 [0.198]
- [Centerline, Matrix \(mm \[in\]\)](#) = 2.54 x 2.54 [.100 x .100]

Contact Related Features:

- [Contact Mating Area Plating Material](#) = Gold (30)
- Contact Material = Phosphor Bronze
- Contact Type = Short Point

Housing Related Features:

- Housing Entry Style = Top
- Housing Material = Thermoplastic
- Housing Flammability Rating = UL 94V-0
- Housing Color = Black

Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = ELV compliant, 5 of 6 Compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C

Conditions for Usage:

- High Temperature Compatible = No

Other:

- Brand = AMP