


292175-8 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



292175-8

✓ [Active](#)

2mm AMP CT

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Connector
- Connector Type = MT (Mass Termination)
- Mating Type = Header
- Number of Positions = 8
- Number of Rows = 1

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [ON TAPING \(EMBOSS\) SMT TYPE POST HDR ASS'Y\(V\) W/O B...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version A)
- [3D Model](#) (IGES, Version A)
- [3D Model](#) (STEP, Version A)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector
- [Connector Type](#) = MT (Mass Termination)
- [Mating Type](#) = Header
- [Number of Positions](#) = 8
- [PCB Mount Style](#) = Surface Mount
- [PCB Mount Angle](#) = Right Angle
- [PCB Polarization](#) = No
- [PCB Retention Feature](#) = No

Mechanical Attachment:

- [Panel Attachment](#) = Without

Termination Related Features:

- Solder Tail Contact Plating = Tin

Body Related Features:

- [Number of Rows](#) = 1
- [Header Body Style](#) = Shrouded
- Centerline (mm [in]) = 2.00 [0.079]

Contact Related Features:

- Contact Material = Brass
- Contact Mating Area Plating = Tin

Housing Related Features:

- [Housing Material](#) = PPS
- [Housing Color](#) = Natural
- Housing Flammability Rating = UL 94V-0

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- [Terminate To](#) = Printed Circuit Board

Packaging Related Features:

- Packaging Method = Emboss on Reel
- Packaging Quantity = 700

Other:

- Brand = AMP