

1051013-1 Product Details

Share Print Email



1051013-1

TE Internal Number: 1051013-1
 Active

SMA/QMA RF Connectors

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Applies To Coaxial Cable
- Connector - RF
- RF Connector Type = SMA
- Jack
- Without Snap-Lock

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [OSM BULKHEAD FEATHRU CABLE JACK - DIRECT SOLDER ATT...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- [OSM Bulkhead Feedthrough Cable Jack Direct Solder At...](#) (PDF, English)

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector - RF
- [RF Connector Type](#) = SMA
- [Gender](#) = Jack
- [Retractable Collar](#) = Without
- [Dielectric Material](#) = TFE Fluorocarbon

Mechanical Attachment:

- [Panel Mount Retention](#) = With
- [Panel Mount Retention Type](#) = Bulkhead
- [Panel Attachment Style](#) = Rear Mount

Electrical Characteristics:

- [Impedance \(Ω\)](#) = 50
- [Frequency](#) = DC - 18 GHz
- [Insulation Resistance \(MΩ\)](#) = 10,000

Termination Features:

- [Coaxial Cable Termination Type](#) = Solder

Dimensions:

- [Length \(mm \[in\]\)](#) = 19.30 [0.760]

Body Features:

- [Snap-Lock](#) = Without
- [Body Style](#) = Straight
- [Body Material](#) = Stainless Steel
- [Body Finish](#) = Gold
- [Shrink Tubing](#) = Without
- [Lockwasher Material](#) = Stainless Steel
- [O-Ring Material](#) = Silicone Rubber

Contact Features:

- [Center Contact](#) = With
- [Center Contact Material](#) = Beryllium Copper
- [Center Contact Plating](#) = Gold over Copper

Configuration Features:

- [Coaxial Cable Type \(RG/U or Mfg.\)](#) = 402 Semi-Rigid/3.58 [.141]

Industry Standards:

- [Government/Industry Qualification](#) = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Conditions for Usage:

- [Applies To](#) = Coaxial Cable

Other:

- [Brand](#) = AMP

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

