


1658525 -2 Product Details

1658525 -2
 [Active](#)
Ribbon Cable Connectors (AMP - LATCH)
[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Connector Type = DIP (Dual In Line Package)
- ? Number of Positions = 34
- ? Plug
- ? Without Mating Polarization
- ? Terminate To Printed Circuit Board

[View all Features](#)
Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information
Product Drawings:

- ? [CONNECTOR, SLIMLINE PCB \(STANDARD\), LEAD FREE](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)
Product Features

(Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Connector Type](#) = DIP (Dual In Line Package)
- ? [Number of Positions](#) = 34
- ? Gender = Plug
- ? [Mating Polarization](#) = Without
- ? [Mounting Ears](#) = Without
- ? PCB Retention Feature = No
- ? Mating Connector Lock = Without
- ? Strain Relief = Without

Termination Related Features:

- ? [Solder Tail Contact Plating](#) = Tin over Nickel

Body Related Features:

- ? Centerline, Matrix (mm [in]) = 2.54 x 2.54 [.100 x .100]

Contact Related Features:

- ? [Contact Mating Area Plating](#) = Tin
- ? Contact Type = Flat
- ? Contact Material = Beryllium Copper

Housing Related Features:

- ? [Housing Color](#) = Blue
- ? Housing Material = Thermoplastic Glass reinforced
- ? Housing Flammability Rating = UL 94V -0

Configuration Related Features:

- ? Cable Stop = Without

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not reviewed for lead free solder process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? [Terminate To](#) = Printed Circuit Board

Other:

- ? Brand = AMP