

1986713-2 Product Details

 [Share](#)  [Print](#)  [Email](#)



Terminal Block Connectors

 [Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- Connector
- Type of Connector = Wire Receptacle
- Not Shrouded
- Housing Color = Green
- Side Stackable

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

TE Internal Number: 1986713-2

 [Active](#)

 [Add to My Part List](#)

 [Request Sample](#)

 [Find Similar Products](#)

 [Buy Product](#)

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none">• POWER TERMINAL BLOCK, SOLDERABLE UP TO 275DEG C DOUB... (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none">• None Available <p>Product Specifications:</p> <ul style="list-style-type: none">• None Available <p>Application Specifications:</p> <ul style="list-style-type: none">• None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none">• None Available <p>CAD Files:</p> <ul style="list-style-type: none">• None Available	<p>Additional Information:</p> <ul style="list-style-type: none">• Product Line Information <p>Related Products:</p> <ul style="list-style-type: none">• Tooling
List all Documents	

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none">• Product Type = Connector• Type of Connector = Wire Receptacle• Shrouded = No• Mount Angle = Vertical• UL File Number = E60677 <p>Electrical Characteristics:</p> <ul style="list-style-type: none">• Current Rating, Max. (A) = 130• Voltage (VAC) = 600 <p>Body Features:</p> <ul style="list-style-type: none">• Side Stackable = Yes• Number of Positions = 2• Number of Rows = Single• Centerline (mm [in]) = 15.00 [0.591]• Wire Entry Diameter (Solid Wire) (mm²) = 0.50 – 41.00• Wire Entry Diameter (Stranded Wire) (mm²) = 0.50 – 41.00• Wire Entry Angle = Side• Interlock = Without• Wire Range (mm [AWG]) = 0.50-41.00 [20-1]• Pin Length (mm [in]) = 5.00 [0.197]	<p>Contact Features:</p> <ul style="list-style-type: none">• Threaded Flange = Without• Screw Flange = Without• Contact Plating, Mating Area, Material = Tin over Steel <p>Housing Features:</p> <ul style="list-style-type: none">• Housing Color = Green• Housing Material = Polyamide <p>Industry Standards:</p> <ul style="list-style-type: none">• RoHS/ELV Compliance = RoHS compliant, ELV compliant• Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C• RoHS/ELV Compliance History = Always was RoHS compliant <p>Other:</p> <ul style="list-style-type: none">• Brand = Tyco Electronics