

5-5583485 -6 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



5-5583485 -6

[Active](#)

.100, .125, .150, .156 C/L Twin Leaf Mother Board Connectors

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Connector
- ? 65 Dual Positions
- ? 2.54 mm Centerline
- ? Post Type = Solder Post
- ? Without End Caps

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? None Available

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? [Connector, Twin Leaf](#) (PDF, English)

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Connector
- ? [Number of Dual Positions](#) = 65
- ? [Post Type](#) = Solder Post

Termination Related Features:

- ? [Termination \(Solder\) Post Length \(mm \[in\]\)](#) = 4.32 [0.170]
- ? Solder Tail Contact Plating = Tin

Body Related Features:

- ? [Centerline \(mm \[in\]\)](#) = 2.54 [0.100]

Contact Related Features:

- ? [Contact Mating Area Plating Material](#) = Gold (15)
- ? Contact Material = Phosphor Bronze
- ? Contact Underplating = Nickel (30)

Housing Related Features:

- ? Housing Material = Polyester GF
- ? Housing Flammability Rating = UL 94V -0

Configuration Related Features:

- ? [End Caps](#) = Without

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- ? Brand = Tyco Electronics