


5650858 - 5 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



5650858 - 5

✓ [Active](#)

Eurocard Type B

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Mating Type = Receptacle
- ? Number of Positions = 32
- ? PCB Mount Angle = Vertical
- ? Post Type = Solder Post
- ? Not Make First / Break Last

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [View Mating Products \(7\)](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Documents are temporarily unavailable. We are working hard to correct the problem. Please try again later.

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)
- ? [Mating Products \(7\)](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Mating Type](#) = Receptacle
- ? [Number of Positions](#) = 32
- ? [PCB Mount Angle](#) = Vertical
- ? [Post Type](#) = Solder Post
- ? [Make First / Break Last](#) = No
- ? [DIN Level](#) = II
- ? [Size](#) = Half
- ? [PCB Retention Feature](#) = No
- ? Color = Gray
- ? Comment = Contact Finish: DIN 41612 Class 2 In Contact Area. Tin On Posts.

Termination Related Features:

- ? [Termination \(Solder\) Post Length \(mm \[in\]\)](#) = 4.57 [0.180]

Body Related Features:

- ? [Contact Cross Section \(mm \[in\]\)](#) = 0.30 x 0.61 [.012 x .024]
- ? Rows Loaded = A, B

Contact Related Features:

- ? Contact Material = Copper Alloy

Housing Related Features:

- ? Housing Material = Polymer
- ? Housing Flammability Rating = UL 94V -0

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? [Flux - Tight Coating](#) = Without
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? Terminate To = Printed Circuit Board

Other:

- ? Brand = AMP