


# 1051650-1 Product Details

Share | Print | Email



1051650-1

TE Internal Number: 1051650-1

Active

## SMA/QMA RF Connectors

Always EU RoHS/ELV Compliant (Statement of Compliance)

### Product Highlights:

- Applies To Coaxial Cable
- Connector - RF
- RF Connector Type = SMA
- Plug
- Without Snap-Lock

[View all Features](#)

### Quick Links

- ▶ Pricing & Availability
- ▶ Search for Tooling
- ▶ Product Feature Selector
- ▶ Contact Us About This Product

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

## Documentation & Additional Information

### Product Drawings:

- [OSM STRAIGHT CABLE PLUG CRIMP ATTACHMENT \(PDF, English\)](#)

### Catalog Pages/Data Sheets:

- None Available

### Product Specifications:

- None Available

### Application Specifications:

- None Available

### Instruction Sheets:

- [OSM Straight Cable Plug Crimp Attachment 1311063-1, ... \(PDF, English\)](#)

### CAD Files:

- None Available

### Related Products:

- [Tooling](#)

[List all Documents](#)

## Product Features (Please use the Product Drawing for all design activity)

### Product Type Features:

- [Product Type](#) = Connector - RF
- [RF Connector Type](#) = SMA
- [Gender](#) = Plug
- [Retractable Collar](#) = Without
- [Dielectric Material](#) = TFE Fluorocarbon
- [Coupling Nut Material](#) = Stainless Steel
- [Coupling Nut Finish](#) = Gold over Nickel

### Mechanical Attachment:

- [Panel Mount Retention](#) = Without
- [Safety Wire Holes](#) = Without

### Electrical Characteristics:

- [Frequency](#) = 12.4 GHz (Max.)
- [Insulation Resistance \(MΩ\)](#) = 10,000

### Termination Features:

- [Coaxial Cable Termination Type](#) = Crimp
- [Crimp Type](#) = Hex

### Dimensions:

- [Length \(mm \[in\]\)](#) = 30.15 [1.187]

### Body Features:

- [Snap-Lock](#) = Without
- [Body Style](#) = Straight
- [Body Material](#) = Stainless Steel
- [Body Finish](#) = Gold
- [Shrink Tubing](#) = With
- [Gasket Material](#) = Silicone Rubber
- [Ferrule Material](#) = Copper
- [Ferrule Plating](#) = Gold over Copper
- [Retaining Ring Material](#) = Beryllium Copper

### Contact Features:

- [Center Contact](#) = With
- [Center Contact Material](#) = Beryllium Copper
- [Center Contact Plating](#) = Gold over Copper

### Configuration Features:

- [Coaxial Cable Type \(RG/U or Mfg.\)](#) = 142, 223, 400, 55

### Industry Standards:

- [Government/Industry Qualification](#) = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

### Conditions for Usage:

- [Applies To](#) = Coaxial Cable

### Other:

- [Brand](#) = AMP

## Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

## Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

## Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

## Keep Me Informed

