


280619-1 Product Details

[Live Product Chat](#)



280619-1

TE Part Number: 280619-1

[Active](#)

[Add to Part List](#)

.156 Inch AMPMODU .031 X .062 Mod I

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Header
- Right Angle Mount Angle
- Box
- Tin (150) Contact Mating Area Plating Material
- Not Keyed

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- [AMP-MODU MOD. 1 RIGHT ANGLE POST SUPPORT ASS'Y \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Header
- Mount Angle = Right Angle
- [Keyed](#) = No
- [Number of Positions](#) = 10

Mechanical Attachment:

- [Mating Post Length \(mm \[in\]\)](#) = 10.00 [0.394]

Termination Related Features:

- Termination End Plating = Tin (150)

Body Related Features:

- Number of Rows = Single
- Centerline (mm [in]) = 3.96 [0.156]

Contact Related Features:

- Contact Mating Area Plating Material = Tin (150)
- Contact Material = Phosphor Bronze

Housing Related Features:

- Housing Material = Polycarbonate
- Housing Color = Green
- Housing Flammability Rating = UL 94V-1

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Terminate To = Printed Circuit Board

Packaging Related Features:

- Packaging Method = Box

Other:

- Brand = AMP