

## 440054-4 Product Details

 **Live Product Chat** US Only  
8:30am - 5pm ET, Mon - Fri



**440054-4**

 [Active](#)

### High Performance Interconnects (HPI)

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

#### Product Highlights:

- 2.00 mm Centerline
- Header
- Number of Positions = 4
- Housing Color = Natural
- Vertical Mount Angle

[View all Features](#) | [Find Similar Products](#)

### Quick Links

[Check Pricing & Availability](#)  
[Search for Tooling](#)  
[View Mating Products \(5\)](#)  
[Product Feature Selector](#)  
[Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [2.0 MM PITCH HPI VERTICAL POST HEADERS](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- [Metric Interconnect System \(Restricted to Sony Corpo...](#) (PDF, English)

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)
- [Mating Products \(5\)](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Header
- [Number of Positions](#) = 4
- [Mount Angle](#) = Vertical

#### Body Related Features:

- [Centerline \(mm \[in\]\)](#) = 2.00 [0.079]
- [Mount Style](#) = Through-Hole
- [Number of Rows](#) = Single
- Post Material = Brass
- Post Plating = Tin
- PCB Retention Method = Boardlock(s)

#### Housing Related Features:

- [Housing Color](#) = Natural
- Housing Flammability Rating = UL 94V-0
- Housing Material = Nylon 66

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Other:

- Brand = AMP