


## 5536052 -5 Product Details



**5536052 -5**

[Active](#)

### Eurocard Type B

[Always EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

#### Product Highlights:

- ? Mating Type = Plug
- ? Number of Positions = 64
- ? PCB Mount Angle = Right Angle
- ? Post Type = Solder Post
- ? Not Make First / Break Last

[View all Features](#) | [Find Similar Products](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [ASSEMBLY, PIN, EUROCARD, TYPE B, 64 POSITION, 2.64\[...](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? None Available

#### Application Specifications:

- ? [Eurocard Connectors Types B,C,M,Q,R, & Enhanced Typ...](#) (PDF, English)

#### Instruction Sheets:

- ? None Available

#### CAD Files:

- ? None Available

#### Additional Information:

- ? [Product Line Information](#)

#### Related Products:

- ? [Tooling](#)

[List all Documents](#)

### Product Features

(Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? [Mating Type](#) = Plug
- ? [Number of Positions](#) = 64
- ? [PCB Mount Angle](#) = Right Angle
- ? [Post Type](#) = Solder Post
- ? [Make First / Break Last](#) = No
- ? [Bus Type](#) = CIMBUS, STE Bus
- ? [DIN Level](#) = II
- ? [Size](#) = Standard
- ? [PCB Retention Feature](#) = No
- ? Color = Gray

#### Termination Related Features:

- ? [Termination \(Solder\) Post Length \(mm \[in\]\)](#) = 2.65 [0.104]

#### Body Related Features:

- ? [Contact Cross Section \(mm \[in\]\)](#) = 0.64 [.025] Sq.
- ? Rows Loaded = A, B

#### Contact Related Features:

- ? Contact Material = Brass

#### Housing Related Features:

- ? Housing Material = Polyester
- ? Housing Flammability Rating = UL 94V -0

#### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? [Flux-Tight Coating](#) = Without
- ? RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- ? Terminate To = Printed Circuit Board

#### Other:

- ? Brand = AMP