



What can we help you find?

Products

Industries

Resources

About TE

My Account

Innovation

Support Center

Home

>

Products

>

Modular Jacks & Plugs

>

Product Feature Selector

>

Product Details

5555153-6 Product Details

Share

Print

Email

5555153-6

TE Internal Number: 5555153-6

Active

View 3D PDF

PCB Mounted Jacks - Single Port, Multi-port and Stacked

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector
- Preloaded
- Single Port Configuration
- 1 x 1 Jack Configuration
- Jack Type = RJ45

[View all Features](#)

Quick Links

- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Add to My Part List

Request Sample

Find Similar Products

Buy Product

Documentation & Additional Information

Product Drawings:

- [MODULAR JACK ASSEMBLY, SHIELDED, 8 POSITION, LOW PRO...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [Modular Plugs, Thru-Hole and Surface Mount Jacks, Da...](#) (PDF, English)

Application Specifications:

- [Modular Jacks](#) (PDF, English)

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- [2D Drawing](#) (DXF, Version C)
- [3D Model](#) (IGES, Version C)
- [3D Model](#) (STEP, Version C)

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Panel Cutout](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector
- Jack Type = RJ45
- PCB Mounting Orientation = Side Entry (Right Angle)
- PCB Mount Style = Through Hole
- Termination Method to PC Board = Solder
- Performance Category = Cat 3
- LED = Without
- Grounding Options = PCB Ground
- Panel Stops = With
- Keyed = No
- Profile = Low
- Color = Black
- Shield Material = Copper Alloy
- Latch Style = Standard

Mechanical Attachment:

- Panel Mount Retention = With
- Flanged = No

Electrical Characteristics:

- Shielded = Yes

Termination Features:

- Solder Tail Contact Plating = Tin over Nickel

Dimensions:

- Height (mm [in]) = 12.70 [0.500]
- PCB Tail Length (mm [in]) = 2.29 [0.091]
- PCB Thickness, Recommended (mm [in]) = 1.57 [0.062]

Body Features:

- Inverted Jack Face = No
- Shield Plating = Tin
- PCB Ground Tab Location (mm [in]) = 3.05 [0.120]

Contact Features:

- Contact Plating, Mating Area, Material = Gold (50)
- Contact Base Material = Phosphor Bronze

Housing Features:

- Housing Material = PBT - GF
- UL Flammability Rating = UL 94V-0

Configuration Features:

- Preloaded = Yes
- Port Configuration = Single
- Jack Configuration = 1 x 1
- Number of Positions = 8
- Number of Contacts Loaded = 8
- Number of PCB Ground Tabs = 2

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Features:

- Packaging Method = Tray
- Packaging Quantity = Bulk

Product Availability:

- Region = Asia, North America

Other:

- Brand = AMP

Corporate Information

About TE

Investors

News Room

Supplier Portal

Careers

Terms & Conditions

Privacy Policy

Quick Links

Distributor Inventory

Product Cross Reference

Documents & Drawings

Product Compliance Support Center

Site Map

Customer Support

Email or Chat With Us

Find a Phone Number

Knowledge Base

Manage Your Account

Keep Me Informed

© 2013 Tyco Electronics Corporation, a TE Connectivity Ltd. company. All Rights Reserved

Provide Website Feedback