


## 88117 -9 Product Details

**Live Product Chat** US Only  
8:30am - 5pm ET, Mon - Fri



**88117 -9**

TE Part Number: 88117 -9

[Active](#)

[Add to Part List](#)

### Flexible Film Contacts

[Always EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

#### Product Highlights:

- ? Pin
- ? Contact Type = Pin
- ? 2.54 mm Centerline
- ? Wire/Cable Type = Flexible Flat Conductor Cable
- ? Gold (15) Contact Mating Area Plating Material

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [View Housings \(55\)](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [CONTACT, .025 SQ PIN](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? None Available

#### Application Specifications:

- ? [Flexible Flat Cable \(FFC\) Housings with Contact Cavi...](#) (PDF, English)

#### Instruction Sheets:

- ? None Available

#### CAD Files:

- ? None Available

#### Additional Information:

- ? [Product Line Information](#)

#### Related Products:

- ? [Tooling](#)
- ? [Housings \(55\)](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? Pin/Socket = Pin
- ? [Wire/Cable Type](#) = Flexible Flat Conductor Cable
- ? Wire Termination Type = Sequential Termination
- ? Comment = For use in housings.

#### Termination Related Features:

- ? Solder Tail Contact Plating = Gold Flash

#### Body Related Features:

- ? [Centerline \(mm \[in\]\)](#) = 2.54 [0.100]
- ? Conductor Width (mm [in]) = 1.19 [0.047]

#### Contact Related Features:

- ? [Contact Type](#) = Pin
- ? [Contact Mating Area Plating Material](#) = Gold (15)
- ? Contact Underplating = Nickel (50)

#### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

#### Packaging Related Features:

- ? [Packaging Method](#) = Strip

#### Other:

- ? Brand = AMP