Miniature relay

DS2Y RELAYS

D 1R



FEATURES

- 1. 2 Form C contact
- 2. High sensitivity-200 mW nominal operating power
- 3. High breakdown voltage 1500 V FCC surge between open contacts
- 4. DIP-2C type matching 16 pin IC socket
- 5. Sealed construction
- 6. Sealed according to RTIII (IP67)

TYPICAL APPLICATIONS

- 1. Telecommunication equipment
- 2. Office equipment
- 3. Computer peripherals
- 4. Security alarm systems
- 5. Medical equipment

ORDERING INFORMATION

DS2Y-S

Operating function Nil: Single side stable

Nominal coil voltage DC 1.5, 3, 5, 6, 9, 12, 24, 48 V

Polarity Nil: Standard polarity

Note: UL/CSA approved type is standard.

TYPES

Contact arrangement	Nominal apil voltage	Single side stable type		
	Nominal coil voltage	Part No.		
2 Form C	1.5V DC	DS2Y-S-DC1.5V		
	3V DC	DS2Y-S-DC3V		
	5V DC	DS2Y-S-DC5V		
	6V DC	DS2Y-S-DC6V		
	9V DC	DS2Y-S-DC9V		
	12V DC	DS2Y-S-DC12V		
	24V DC	DS2Y-S-DC24V		
	48V DC	DS2Y-S-DC48V		

Standard packing: Tube: 50 pcs.; Case: 500 pcs.

RATING

1. Coil data


Single side stable type

Nominal coil voltage	Pick-up voltage (at 20°C 68°F)	Drop-out voltage (at 20°C 68°F)	Nominal operating current [±10%] (at 20°C 68°F)		Coil resistance [±10%] (at 20°C 68°F)	Nominal operating power	Max. applied voltag (at 50°C 122°F)	
1.5V DC			132.7mA		11.3Ω	200mW	200%V of nominal voltage	
3V DC		10%V or more of nominal voltage (Initial)	66.7mA		45Ω			
5V DC			40mA		125Ω			
6V DC	70%V or less of		33.3mA		180Ω			
9V DC	nominal voltage (Initial)		22.2mA		405Ω			
12V DC	(IIIIdi)		16.7mA		720Ω			
24V DC			8.3mA		2,880Ω			
48V DC			6.3mA		7,680Ω	300mW		
2. Specification	6							
Characteristics				Specifications				
	Arrangement			2 Form C				
Contact	Initial contact resistance, max.			Max. 50 mΩ (By voltage drop 6 V DC 1A)				
	Contact material			Ag+Au clad				
Rating	Max. switching power			60 W, 62.5 VA (resistive load)				
	Max. switching voltage			220 V DC, 250 V AC				
	Max. switching current			2 A				
	Max. carrying current			3 A				
	Minimum operating power			Approx. 98 mW (147 mW: 48 V)				
	Nominal operating power			Approx. 200 mW (300 mW: 48 V)				
Electrical characteristics	Insulation resistance (Initial)			Min. 100M Ω (at 500V DC) Measurement at same location as "Initial breakdown voltage" section.				
	Breakdown voltage (Initial)	Between open contacts		750 Vrms for 1min. (Detection current: 10mA.)				
		Between contact sets		1,000 Vrms for 1min. (Detection current: 10mA.)				
		Between contact and coil		1,000 Vrms for 1min. (Detection current: 10mA.)				
	FCC surge breakdown voltage between contacts and coil			1,500 V				
	Temperature rise (at 20°C 68°F)			Max. 65°C with nominal coil voltage across coil and at nominal switching capacity				
	Operate time [Set time] (at 20°C 68°F)			Approx. 4 ms [approx. 3 ms] (Nominal coil voltage applied to the coil, excluding contact bounce time.)				
	Release time [Reset time] (at 20°C 68°F)			Approx. 3 ms [approx. 3 ms] (Nominal coil voltage applied to the coil, excluding contact bounce time.) (without diode)				
Mechanical characteristics	Functional			Min. 490 m/s ² (Half-wave pulse of sine wave: 11 ms; detection time: 10µs.)				
	Shock resistance	Destructive			(Half-wave pulse of sine wave: 6 ms.)			
		Functional	10 to 55 Hz ;		at double amplitude of 3.3 mm (Detection time: 10µs.)			
	Vibration resistance Destructive			10 to 55 Hz at double amplitude of 5 mm				
F 1 1 1 1	Mechanical			Min. 10 ⁸				
Expected life	Electrical			5×10 ⁵ (1 A 30 V DC), 10 ⁵ (2 A 30 V DC)				
Conditions	Conditions for operation, transport and storage*		e*	Ambient temperature: -40°C to +70°C -40°F to +158°F Humidity: 5 to 85% R.H. (Not freezing and condensing at low temperature)				
	Max. operating speed (at rated load)			60 times/min.				
Unit weight				Approx. 4g .14oz				

* Refer to "6. Usage, Storage and Transport Conditions" in AMBIENT ENVIRONMENT section in Relay Technical Information.

REFERENCE DATA


1. Maximum switching capacity



4-(1) Influence of adjacent mounting Tested sample: DS2Y-S-DC12V, 10 pcs. Ambient temperature: 20°C 68°F


TEST METHOD

- 1. Apply nominal voltage to No. (1) and (3) DS2Y relays.
- 2. Measure pick-up voltage and drop-out voltage of No. (2) relay when inter-relay distance (l) changes.



DIMENSIONS (mm inch)


Single side stable



General tolerance: ±0.3 ±.012

2. Coil temperature rise (Single side stable) Tested sample: DS2Y-S-DC12V, 5 pcs. Measured portion: Inside the coil


Ambient temperature: 21°C to 25°C 70°F to 77°F



4-(2) Influence of adjacent mounting Tested sample: DS2Y-S-DC12V, 10 pcs. Ambient temperature: 20°C 68°F

TEST METHOD

- 1. Apply nominal voltage to No. (1) and (3) DS2Y relays.
- 2. Measure pick-up voltage and drop-out voltage of No. (2) relay when inter-relay distance (ℓ) changes.



8-0.9 dia.

2.54

7.62


2.54


matching 16 pin IC socket

Tolerance: ±0.1 ±.004

3. Operate/release time for single side stable (Without diode)

Tested sample: DS2Y-S-DC12V, 10 pcs. Ambient temperature: 20°C 68°F





Direction indication*

*A polarity bar shows the relay direction.

For Cautions for Use, see Relay Technical Information.

Download CAD Data from our Web site.