

# **Panasonic** ideas for life

## TV-5 rated. High sensitivity: 250mW 1a 5A power relays





## **FEATURES**

#### 1. High sensitivity

A nominal operating power of 250mW and high sensitivity make it ideal for energy saving (LK relay is 530mW).

### 2. High insulation resistance between contact and coil

- 1) Creepage distance and clearances between contact and coil: Min. 6 mm .236 inch (In compliance with IEC60065)
- 2) Surge withstand voltage between contact and coil: 10,000 V
- 3. Popular terminal pitch in AV equipment field

#### 4. Space-saving slim type

Base area: Width 11 × Length 24 mm Width .433 × Length .945 inch

#### 5. Conforms to the various safety standards


UL, CSA, VDE, TÜV and SEMKO approved

## TYPICAL APPLICATIONS

- Audio visual equipment
- Office equipment
- Home appliances

**RoHS** compliant

## ORDERING INFORMATION



Notes: Certified by UL, CSA, TÜV and SEMKO

VDE approved type is available. Please consult us for details.

## **TYPES**

Contact arrangement	Nominal coil voltage	Part No.				
	5V DC	LKS1aF-5V				
1 Form A	9V DC	LKS1aF-9V				
I FOIII A	12V DC	LKS1aF-12V				
	24V DC	LKS1aF-24V				


Standard packing Carton: 100 pcs. Case: 500 pcs.

Note: 6 V, 18 V DC types are also available. Please consult us for details.

## **RATING**

#### 1. Coil data

Nominal coil voltage	Pick-up voltage (at 20°C 68°F)	Drop-out voltage (at 20°C 68°F)	Nominal operating current [±10%] (at 20°C 68°F)	Coil resistance [±10%] (at 20°C 68°F)	Nominal operating power	Max. applied voltage (at 20°C 68°F)
5V DC	70%V or less of nominal voltage (Initial)	10%V or more of nominal voltage (Initial)	50mA	100Ω		6.5V DC
9V DC			27.8mA	324Ω	250mW	11.7V DC
12V DC			20.8mA	576Ω	25011100	15.6V DC
24V DC			10.4mA	2,304Ω		31.2V DC



#### 2. Specifications


Characteristics		Item	Specifications					
Contact	Arrangement		1 Form A					
	Contact resistance (Initial)		Max. 100 mΩ (By voltage drop 6 V DC 1A)					
	Contact material		AgSnO₂ type					
Rating	Nominal switching ca	pacity (resistive load)	5A 277V AC					
	Max. switching powe	r (resistive load)	1,385VA					
	Max. switching voltage		277V AC					
	Max. switching currer	nt	5A (AC)					
	Min. switching capac	ity*1	100mA, 5V DC					
	Insulation resistance	(Initial)	Min. 1,000M $\Omega$ (at 500V DC) Measurement at same location as "Breakdown voltage" section.					
	Breakdown voltage	Between open contacts	1,000 Vrms for 1 min. (Detection current: 10 mA)					
	(Initial)	Between contact and coil	4,000 Vrms for 1 min. (Detection current: 10 mA)					
Electrical characteristics	Temperature rise (coil)		Max. 35°C 95°F (By resistive method, nominal coil voltage applied to the coil; contact carrying current: 5A, at 70°C 158°F)					
	Surge breakdown vo (Between contact and		10,000 V					
	Operate time (at nominal voltage) (at 20°C 68°F) (Initial)		Max. 15 ms (excluding contact bounce time.)					
	Release time (at nominal voltage) (at 20°C 68°F) (Initial)		Max. 5 ms (excluding contact bounce time) (Without diode)					
	Shock resistance	Functional	200 m/s² (Half-wave pulse of sine wave: 11 ms; detection time: 10μs.)					
Mechanical	SHOCK resistance	Destructive	1,000 m/s² (Half-wave pulse of sine wave: 6 ms.)					
characteristics	Vibration resistance	Functional	10 to 55 Hz at double amplitude of 1.5 mm (Detection time: 10μs.)					
	VIDIATION TESISTANCE	Destructive	10 to 55 Hz at double amplitude of 1.5 mm					
Expected life	Mechanical (at 180 times/min.)		Min. 10 <sup>6</sup>					
Expected life	Electrical (at 20 times/min.)		Min. 10 <sup>5</sup> (ON:OFF = 1.5s:1.5s, at nominal switching capacity)					
Conditions	Conditions for operation, transport and storage*3		Ambient temperature: $-40^{\circ}$ C to $+70^{\circ}$ C $-40^{\circ}$ F to $+158^{\circ}$ F, Humidity: 5 to 85% R.H. (Not freezing and condensing at low temperature), Air pressure: 86 to 106kPa					
	Max. operating speed	b	20 times/min. (at nominal switching capacity)					
Unit weight			Approx. 12 g .42 oz					

Notes: \*1. This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual load.


- \*2. Wave is standard shock voltage of ±1.2×50μs according to JEC-212-1981
- \*3. The upper limit of the ambient temperature is the maximum temperature that can satisfy the coil temperature rise value. Refer to Usage, transport and storage conditions in NOTES.

## REFERENCE DATA


1. Max. switching power (AC resistive load)



2. Coil temperature rise Sample: LKS1aF-12V, 6 pcs. Point measured: coil inside Contact current: 0 A, 5A




3. Ambient temperature characteristics and coil applied voltage Contact current: 5 A




#### 4. Life curve

Operation frequency: 20 times/min. (ON/OFF = 1.5s: 1.5s) Ambient temperature: Room temperature




5-(1). Electrical life test (5 A 277 V AC, resistive load) Sample: LKS1aF-12V, 6 pcs. Operation frequency: 20 times/min. (ON/OFF = 1.5s: 1.5s)Ambient temperature: 20°C 68°F


#### Circuit:



#### Change of pick-up and drop-out voltage



#### Change of contact resistance



5-(2). Electrical life test (UL lamp load test TV-5)

Tested sample: LKS1aF-12V, 6 pcs.

Overload test

Load: 7.5 A 120 V AC (60 Hz),


Inrush: 111 A
Operation frequency: 10 times/min (ON: OFF = 1 s: 5 s)

No. of operations: 50 ope. • Endurance test


Load: 5A 120 V AC (60 Hz), Inrush: 78 A Operation frequency: 10 times/min (ON: OFF = 1 s: 5 s)

No. of operations: 25,000 ope.

#### Change of pick-up and drop-out voltage



#### Change of contact resistance




## **DIMENSIONS** (mm inch)

The CAD data of the products with a CAD Data mark can be downloaded from: http://industrial.panasonic.com/ac/e


## CAD Data




#### External dimensions




**20.0** .787





PC board pattern (Bottom view)



Tolerance:  $\pm 0.1 \pm .004$ 

#### Schematic (Bottom view)



**Dimension:** General tolerance

Less than 1mm .039inch:  $\pm 0.1 \pm .004$ Min. 1mm .039inch less than 3mm .118 inch:  $\pm 0.2 \pm .008$ Min. 3mm .118 inch: ±0.3 ±.012

## **SAFETY STANDARDS**

UL/C-UL (Recognized)		CSA (Certified)		VDE (Certified)		TV rating (UL/CSA)		TÜV (Certified)		SEMKO (Certified)	
File No.	Contact rating	File No.	Contact rating	File No.	Contact rating	File No.	Rating	File No.	Rating	File No.	Contact rating
E43149	5A 277V AC 5A 30V DC 10A 277V AC		5A 277V AC 5A 30V DC 10A 277V AC		10A 250V AC $(\cos\phi = 1.0)$	UL E43149 CSA LR26550	TV-5	B 10 01 13461 270	5A 250V AC (cosφ=1.0)		3/100A 250V AC 5/40A 250V AC

## For Cautions for Use.