




Search bar: What can we help you find?

- Products
- Industries
- Resources
- About TE
- My Account
- Innovation
- Support Center

Home > Products > Terminals & Splices > Product Feature Selector > Product Details

### 326809-1 Product Details

Share | Print | Email



326809-1

TE Internal Number: 326809-1  
Active

View 3D PDF

#### AMPOWER Terminals

Always EU RoHS/ELV Compliant (Statement of Compliance)

#### Product Highlights:

- Product Classification = Connectors - Terminals and Splices
- Power Generation and Distribution Application
- Wire Size (AWG/CM) = 600,000 CM
- Wire/Cable Size = 550,000 - 650,000 CMA
- Terminal Configuration = Standard

View all Features

Add to My Part List | Request Sample | Find Similar Products | Buy Product

#### Quick Links

- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

#### Documentation & Additional Information

##### Product Drawings:

- TERMINAL, AMPOWER, WIRE SIZE: 600 MCM (PDF, English)

##### Catalog Pages/Data Sheets:

- None Available

##### Product Specifications:

- None Available

##### Application Specifications:

- None Available

##### Instruction Sheets:

- None Available

##### CAD Files: (CAD Format & Compression Information)

- 2D Drawing (DXF, Version AE)
- 3D Model (IGES, Version AE)
- 3D Model (STEP, Version AE)

##### Related Products:

- Tooling

List all Documents

#### Product Features (Please use the Product Drawing for all design activity)

##### Product Type Features:

- Product Classification = Connectors - Terminals and Splices
- Terminal Configuration = Standard
- Stud Size = 3/8 [9.53]
- Stud Diameter (mm [in]) = 9.53 [0.375]
- Finish = Tin

##### Termination Features:

- Wire/Cable Size (CMA) = 550,000 - 650,000

##### Dimensions:

- Barrel I.D. Min. (mm [in]) = 27.31 [1.075]

##### Body Features:

- Wire Size (AWG/CM) = 600,000 CM
- Stud Hole Diameter (mm [in]) = 9.91 [0.390]
- Barrel Length = Standard
- Material = Copper (Annealed) per ASTM B-75
- Inspection Slot = Without
- Body Style = Straight
- Tongue Material Thickness (mm [in]) = 5.59 [0.220]

##### Configuration Features:

- Number of Holes = 2

##### Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

##### Operation/Application:

- Application = Power Generation and Distribution

##### Packaging Features:

- Packaging Quantity = 25

##### Other:

- Brand = AMP
- Comment = Electrodeposited Tin Plate per MIL-T-10727.; Two Crimps necessary.

#### Corporate Information

- About TE
- Investors
- News Room
- Supplier Portal
- Careers
- Terms & Conditions
- Privacy Policy

#### Quick Links

- Distributor Inventory
- Product Cross Reference
- Documents & Drawings
- Product Compliance Support Center
- Site Map

#### Customer Support

- Email or Chat With Us
- Find a Phone Number
- Knowledge Base
- Manage Your Account

#### Keep Me Informed

