


Timing Mode:

Timing cycle begins upon application of power to the heater terminals. At the end of the initial delay time the relay contacts transfer and remain in a transferred state until input power is removed. When the heater input power is removed, the contacts transfer back to their original state at the end of a reset (release) delay period.

Timing Diagram:



Contact Information:

Arrangement: 1 form A (SPST - Normally open) - Delay on Make 1 form B (SPST - Normally closed) - Delay on Break Contact Material: Silver - Cadmium Oxide Rating (Resistive): 3A @ 115V AC Expected Life @ 25°C: 500,000 operations minimum at rated loads


Environmental Information:


Temperature Range: Operating & storage: -55°C to +80°C, (-67°F to +176°F)

Mechanical Information:

Termination & Enclosure: Octal style, or 9-pin miniature style glass envelope. See Diagram A & B. Weight: 1 oz. (28g)

Outline Dimensions:





Timing Specifications:

Timing - Fixed: 1 through 300 secs. - (octal style) or 1 - 120 secs. (9-pin miniature style) Timing Tolerance: ±20% - Tighter tolerances are available. Repeatability: ±5% Release Time: Contact factory Timing Cycle Interrupt Transfer: none

Initial Dielectric Strength:


1-10 Second Type: Between open contacts: 250V RMS; Between contacts & coil: 500V RMS
15 - 300 Second Type: Between open contacts: 800V RMS; Between contacts & coil: 500V RMS

Input Information:

Voltage: AC or DC - 6V, 12V, 26V, 50V and 115V. **Other voltages are available.** Power Requirement: 2.0 Watts approx. Transient Protection: impervious to transients Polarity Protection: None required


Input Voltages & Limits:

Nominal	Minimum	Maximum
6V AC/DC	4V	8V
12V AC/DC	10V	14V
26V AC/DC	22V	30V
50V AC/DC	42	58V





Wiring Diagrams:





Ordering Information: Definition of a part number for the Amperite G Series Time Delay Relay. Example:

<u>115</u>	<u>NO</u>	<u>60</u>	Ι
4	4	4	4
Á	в́	ć	Ď

A: Denotes nominal Input voltage. Voltages Available: 6, 12, 26, 50 & 115V AC/DC. Custom Voltages are available.

B: Denotes contact form: NO = normally open (Delay on Make) -1 form A - SPST C = normally closed (Delay on Break) -1 form B - SPST

C: Denotes timing value: Factory preset time delays from 1 - 300 secs. are available (octal style) and 1 - 120 secs. (9-pin miniature style)

D: Denotes type of glass envelope: Blank = octal style. T = 9-pin miniature style.

